

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P265082

Luminaire Tested: **LD2B15D010 EU2B1510SP159040 2LBDL*LI**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P265082
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1711-432-2)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B15D010 EU2B1510SP159040 2LBDL*LI
Description: 1500 Lumen, 2inch Portfolio LED Downlight
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1110.0 lumens
Efficiency: N/A
Efficacy: 77.6 lumens/watt
Spacing Criteria (0/90/45): 0.31 / 0.31 / 0.32
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P265082

CATALOG NUMBER: LD2B15D010 EU2B1510SP159040 2LBDL*LI

Luminous Intensity Polar Plot





TEST NUMBER: P265082

CATALOG NUMBER: LD2B15D010 EU2B1510SP159040 2LBDL*LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20								
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR																																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																											
1	115	113	111	110	113	111	110	108	107	106	105	104	103	102	100	99	99	97																											
2	112	108	106	103	110	107	104	102	104	102	100	101	99	98	98	97	96	94																											
3	109	104	101	98	107	103	100	97	100	98	96	98	96	94	96	94	93	92																											
4	105	100	97	94	104	99	96	93	97	95	92	96	93	91	94	92	90	89																											
5	103	97	93	91	101	96	93	90	95	92	89	93	91	89	92	90	88	87																											
6	100	94	90	88	99	94	90	87	92	89	87	91	88	86	90	88	86	85																											
7	98	92	88	85	97	91	88	85	90	87	85	89	86	84	88	86	84	83																											
8	95	89	86	83	94	89	85	83	88	85	82	87	84	82	86	84	82	81																											
9	93	87	83	81	92	87	83	81	86	83	81	85	82	80	85	82	80	79																											
10	91	85	82	79	91	85	81	79	84	81	79	84	81	79	83	80	78	78																											

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	3918526
5°	3189287
10°	1722795
15°	686929
20°	275428
25°	131900
30°	68362
35°	36137
40°	20030
45°	12419
50°	8520
55°	5763
60°	4342
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P265082

CATALOG NUMBER: LD2B15D010 EU2B1510SP159040 2LBDL*LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	517.9	46.7
10°-20°	408.6	36.8
20°-30°	120.5	10.9
30°-40°	40.1	3.6
40°-50°	15.1	1.4
50°-60°	6.7	0.6
60°-70°	1.1	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1047.1	94.3
0°-40°	1087.2	97.9
0°-60°	1109.0	99.9
0°-90°	1110.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1110.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7942	
5°	6440	518
15°	1345	409
25°	242	121
35°	60	40
45°	18	15
55°	7	7
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P265082

CATALOG NUMBER: LD2B15D010 EU2B1510SP159040 2LBDL*LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	7942.5
2.5°	7622.4
5°	6439.8
7.5°	4961.6
10°	3438.9
12.5°	2200.7
15°	1344.9
17.5°	820.3
20°	524.6
22.5°	351.2
25°	242.3
27.5°	171.2
30°	120.0
32.5°	84.5
35°	60.0
37.5°	42.2
40°	31.1
42.5°	24.5
45°	17.8
47.5°	15.6
50°	11.1
52.5°	8.9
55°	6.7
57.5°	6.7
60°	4.4
62.5°	2.2
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)