

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P265084

Luminaire Tested: **LD2B15D010 EU2B1510SP159040 2LBDL*MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P265084
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1711-432-2)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B15D010 EU2B1510SP159040 2LBDL*MW
Description: 1500 Lumen, 2inch Portfolio LED Downlight
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1109.0 lumens
Efficiency: N/A
Efficacy: 77.6 lumens/watt
Spacing Criteria (0/90/45): 0.31 / 0.31 / 0.32
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P265084

CATALOG NUMBER: LD2B15D010 EU2B1510SP159040 2LBDL*MW

Luminous Intensity Polar Plot





TEST NUMBER: P265084

CATALOG NUMBER: LD2B15D010 EU2B1510SP159040 2LBDL*MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									20
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100											100																	
1	115	113	111	110	113	111	110	108	107	106	105	104	103	102	100	99	99	97											97																	
2	112	108	106	103	110	107	104	102	104	102	100	101	99	98	98	97	96	94											94																	
3	109	104	101	98	107	103	100	97	100	98	96	98	96	94	96	94	93	92											92																	
4	105	100	97	94	104	99	96	93	97	95	92	96	93	91	94	92	90	89											89																	
5	103	97	93	91	101	96	93	90	95	92	89	93	91	89	92	90	88	87											87																	
6	100	94	90	88	99	94	90	87	92	89	87	91	88	86	90	88	86	85											85																	
7	98	92	88	85	97	91	88	85	90	87	85	89	86	84	88	86	84	83											83																	
8	95	89	86	83	94	89	85	83	88	85	82	87	84	82	86	84	82	81											81																	
9	93	87	83	81	92	87	83	81	86	83	81	85	82	80	85	82	80	79											79																	
10	91	85	82	79	91	85	81	79	84	81	79	84	81	79	83	80	78	78											78																	

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	3914974
5°	3186415
10°	1721242
15°	686316
20°	275165
25°	131791
30°	68305
35°	36137
40°	20030
45°	12419
50°	8520
55°	5763
60°	4342
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P265084

CATALOG NUMBER: LD2B15D010 EU2B1510SP159040 2LBDL*MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	517.4	46.7
10°-20°	408.2	36.8
20°-30°	120.4	10.9
30°-40°	40.1	3.6
40°-50°	15.1	1.4
50°-60°	6.7	0.6
60°-70°	1.1	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1046.1	94.3
0°-40°	1086.2	97.9
0°-60°	1107.9	99.9
0°-90°	1109.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1109.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7935	
5°	6434	517
15°	1344	408
25°	242	120
35°	60	40
45°	18	15
55°	7	7
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P265084

CATALOG NUMBER: LD2B15D010 EU2B1510SP159040 2LBDL*MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	7935.3
2.5°	7615.5
5°	6434.0
7.5°	4957.1
10°	3435.8
12.5°	2198.7
15°	1343.7
17.5°	819.5
20°	524.1
22.5°	350.9
25°	242.1
27.5°	171.0
30°	119.9
32.5°	84.4
35°	60.0
37.5°	42.2
40°	31.1
42.5°	24.4
45°	17.8
47.5°	15.5
50°	11.1
52.5°	8.9
55°	6.7
57.5°	6.7
60°	4.4
62.5°	2.2
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)