

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P264397

Luminaire Tested: **LD2B10D010 EU2B1010SP159040 2LBD*WH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P264397
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1805-787-1)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B10D010 EU2B1010SP159040 2LBD*WH
Description: 1000 Lumen, 2inch Portfolio LED Downlight
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 823.9 lumens
Efficiency: N/A
Efficacy: 80.0 lumens/watt
Spacing Criteria (0/90/45): 0.28 / 0.28 / 0.28
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P264397

CATALOG NUMBER: LD2B10D010 EU2B1010SP159040 2LBD*WH

Luminous Intensity Polar Plot





TEST NUMBER: P264397

CATALOG NUMBER: LD2B10D010 EU2B1010SP159040 2LBD*WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	116	114	112	111	113	112	110	109	108	107	106	104	103	102	101	100	100	98				98
2	113	109	107	105	111	108	106	104	105	103	101	102	101	99	99	98	97	96				96
3	110	106	103	100	108	105	102	100	102	100	98	100	98	97	98	96	95	94				94
4	107	103	99	97	106	102	99	96	100	97	95	98	96	94	96	95	93	92				92
5	105	100	97	94	104	99	96	94	98	95	93	96	94	92	95	93	91	90				90
6	103	98	94	92	102	97	94	91	96	93	91	95	92	90	93	91	90	89				89
7	101	95	92	90	100	95	92	89	94	91	89	93	90	89	92	90	88	87				87
8	99	93	90	88	98	93	90	88	92	89	87	91	89	87	91	88	87	86				86
9	97	92	88	86	96	91	88	86	91	88	86	90	87	86	89	87	85	85				85
10	95	90	87	85	95	90	87	85	89	86	85	89	86	84	88	86	84	83				83

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	3888135
5°	3116536
10°	1360241
15°	421535
20°	146954
25°	64888
30°	29396
35°	15298
40°	8695
45°	4117
50°	2610
55°	1462
60°	789
65°	934
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P264397

CATALOG NUMBER: LD2B10D010 EU2B1010SP159040 2LBD*WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	477.9	58.0
10°-20°	261.7	31.8
20°-30°	59.7	7.2
30°-40°	17.2	2.1
40°-50°	5.3	0.6
50°-60°	1.6	0.2
60°-70°	0.7	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	799.2	97.0
0°-40°	816.4	99.1
0°-60°	823.2	99.9
0°-90°	823.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	823.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7881	
5°	6293	478
15°	825	262
25°	119	60
35°	25	17
45°	6	5
55°	2	2
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P264397

CATALOG NUMBER: LD2B10D010 EU2B1010SP159040 2LBD*WH

CANDELA DISTRIBUTION (FULL):

	0°
0°	7880.9
1°	7782.8
2°	7579.0
3°	7262.8
4°	6828.1
5°	6292.9
6°	5636.7
7°	4903.6
8°	4138.3
9°	3397.6
10°	2715.2
11°	2137.7
12°	1682.7
13°	1324.2
14°	1046.0
15°	825.3
16°	651.1
17°	518.3
18°	416.9
19°	339.1
20°	279.9
22.5°	181.0
25°	119.2
26°	100.6
27°	85.4
28°	71.9
29°	60.0
30°	51.6
32.5°	35.5
35°	25.4
37.5°	18.6
40°	13.5
42.5°	9.3
45°	5.9
47.5°	4.2
50°	3.4
52.5°	2.5
55°	1.7
57.5°	0.8
60°	0.8
62.5°	0.8
65°	0.8
67.5°	0.8



TEST NUMBER: P264397

CATALOG NUMBER: LD2B10D010 EU2B1010SP159040 2LBD*WH

CANDELA DISTRIBUTION (continued):

	0°
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







70°		0.0
72.5°		0.0



(END OF REPORT)