

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P225069

Luminaire Tested: **LD2B10D010 EU2B10FL409040 2LBD*WH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P225069
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14829)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B10D010 EU2B10FL409040 2LBD*WH
Description: 1000 Lumen, 2inch Portfolio LED Downlight
FLOOD OPTIC
SPUN ROUND TRIM WITH WHEAT HAZE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 889.9 lumens
Efficiency: N/A
Efficacy: 86.4 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P225069

CATALOG NUMBER: LD2B10D010 EU2B10FL409040 2LBD*WH

Luminous Intensity Polar Plot





TEST NUMBER: P225069

CATALOG NUMBER: LD2B10D010 EU2B10FL409040 2LBD*WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95			95
2	110	106	102	100	108	104	101	98	101	98	96	98	96	94	95	94	92	91			91
3	106	100	96	93	104	99	95	92	96	93	91	94	91	89	92	90	88	87			87
4	102	95	91	87	100	94	90	87	92	89	86	90	87	85	88	86	84	82			82
5	98	91	86	82	96	90	85	82	88	84	81	87	83	81	85	82	80	79			79
6	94	87	82	78	93	86	81	78	85	80	77	83	80	77	82	79	76	75			75
7	91	83	78	75	89	82	78	74	81	77	74	80	76	74	79	76	73	72			72
8	87	79	75	71	86	79	74	71	78	74	71	77	73	70	76	73	70	69			69
9	84	76	71	68	83	76	71	68	75	71	68	74	70	68	73	70	67	66			66
10	81	73	69	65	80	73	68	65	72	68	65	71	68	65	71	67	65	64			64

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	821096
5°	790016
10°	695392
15°	546216
20°	371355
25°	216857
30°	110431
35°	52251
40°	22805
45°	9860
50°	4761
55°	3039
60°	1782
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P225069

CATALOG NUMBER: LD2B10D010 EU2B10FL409040 2LBD*WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	185.6	20.9
10°-20°	370.4	41.6
20°-30°	237.7	26.7
30°-40°	75.4	8.5
40°-50°	16.1	1.8
50°-60°	4.1	0.5
60°-70°	0.5	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	793.7	89.2
0°-40°	869.1	97.7
0°-60°	889.3	99.9
0°-90°	889.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	889.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2120	
5°	2032	186
15°	1362	370
25°	507	238
35°	110	75
45°	18	16
55°	4	4
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P225069

CATALOG NUMBER: LD2B10D010 EU2B10FL409040 2LBD*WH

CANDELA DISTRIBUTION (FULL):

	0°
0°	2119.8
2.5°	2099.5
5°	2031.8
7.5°	1921.3
10°	1768.0
12.5°	1580.8
15°	1362.1
17.5°	1128.7
20°	900.9
22.5°	687.8
25°	507.4
27.5°	361.9
30°	246.9
32.5°	165.7
35°	110.5
37.5°	73.3
40°	45.1
42.5°	28.2
45°	18.0
47.5°	12.4
50°	7.9
52.5°	5.6
55°	4.5
57.5°	3.4
60°	2.3
62.5°	1.1
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)