

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224547

Luminaire Tested: **LD2B15D010 EU2B15FL409040 2LBDL*GPH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P224547
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14831)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B15D010 EU2B15FL409040 2LBDL*GPH
Description: 1500 Lumen, 2inch Portfolio LED Downlight
FLOOD OPTIC
LENSED SPUN ROUND TRIM WITH GRAPHITE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1118.8 lumens
Efficiency: N/A
Efficacy: 78.2 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P224547

CATALOG NUMBER: LD2B15D010 EU2B15FL409040 2LBDL*GPH

Luminous Intensity Polar Plot





TEST NUMBER: P224547

CATALOG NUMBER: LD2B15D010 EU2B15FL409040 2LBDL*GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	95	95	95
2	110	106	102	100	108	104	101	98	101	99	96	98	96	94	95	94	92	91	91	91	91
3	106	100	96	93	104	99	95	92	96	93	91	94	92	89	92	90	88	87	87	87	87
4	102	95	91	87	100	94	90	87	92	89	86	90	87	85	89	86	84	83	83	83	83
5	98	91	86	83	96	90	85	82	88	84	81	87	83	81	85	82	80	79	79	79	79
6	94	87	82	78	93	86	81	78	85	81	78	83	80	77	82	79	77	75	75	75	75
7	91	83	78	75	89	82	78	74	81	77	74	80	76	74	79	76	73	72	72	72	72
8	87	80	75	71	86	79	74	71	78	74	71	77	73	71	76	73	70	69	69	69	69
9	84	76	72	68	83	76	71	68	75	71	68	74	70	68	73	70	68	66	66	66	66
10	81	73	69	65	80	73	68	65	72	68	65	72	68	65	71	67	65	64	64	64	64

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1014924
5°	994421
10°	883597
15°	693226
20°	466245
25°	271264
30°	135880
35°	63411
40°	29580
45°	12490
50°	6026
55°	3849
60°	2247
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P224547

CATALOG NUMBER: LD2B15D010 EU2B15FL409040 2LBDL*GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	234.1	20.9
10°-20°	469.2	41.9
20°-30°	296.7	26.5
30°-40°	92.3	8.3
40°-50°	20.5	1.8
50°-60°	5.2	0.5
60°-70°	0.7	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1000.1	89.4
0°-40°	1092.4	97.6
0°-60°	1118.1	99.9
0°-90°	1118.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1118.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2620	
5°	2558	234
15°	1729	469
25°	635	297
35°	134	92
45°	23	21
55°	6	5
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P224547

CATALOG NUMBER: LD2B15D010 EU2B15FL409040 2LBDL*GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	2620.2
2.5°	2608.8
5°	2557.5
7.5°	2436.2
10°	2246.5
12.5°	2006.9
15°	1728.7
17.5°	1427.8
20°	1131.1
22.5°	864.4
25°	634.7
27.5°	445.0
30°	303.8
32.5°	201.1
35°	134.1
37.5°	89.9
40°	58.5
42.5°	35.7
45°	22.8
47.5°	15.7
50°	10.0
52.5°	7.1
55°	5.7
57.5°	4.3
60°	2.9
62.5°	1.4
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)