

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P225013

Luminaire Tested: **LD2B10D010 EU2B10FL409040 2LBD*WMH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P225013
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14830)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B10D010 EU2B10FL409040 2LBD*WMH
Description: 1000 Lumen, 2inch Portfolio LED Downlight
FLOOD OPTIC
SPUN ROUND TRIM WITH WHEAT METALLIC HAZE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 821.9 lumens
Efficiency: N/A
Efficacy: 79.8 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P225013

CATALOG NUMBER: LD2B10D010 EU2B10FL409040 2LBD*WMH

Luminous Intensity Polar Plot





TEST NUMBER: P225013

CATALOG NUMBER: LD2B10D010 EU2B10FL409040 2LBD*WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	95	95	95
2	110	106	102	100	108	104	101	98	101	98	96	98	96	94	95	94	92	91	91	91	91
3	106	100	96	93	104	99	95	92	96	93	91	94	91	89	92	90	88	87	87	87	87
4	102	95	91	87	100	94	90	87	92	89	86	90	87	85	88	86	84	82	82	82	82
5	98	91	86	82	96	90	85	82	88	84	81	87	83	81	85	82	80	79	79	79	79
6	94	87	82	78	93	86	81	78	85	81	77	83	80	77	82	79	77	75	75	75	75
7	91	83	78	75	89	82	78	74	81	77	74	80	76	74	79	76	73	72	72	72	72
8	87	79	75	71	86	79	74	71	78	74	71	77	73	71	76	73	70	69	69	69	69
9	84	76	71	68	83	76	71	68	75	71	68	74	70	68	73	70	67	66	66	66	66
10	81	73	69	65	80	73	68	65	72	68	65	72	68	65	71	67	65	64	64	64	64

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	745796
5°	730448
10°	647092
15°	508481
20°	341883
25°	198608
30°	99249
35°	46813
40°	22147
45°	9696
50°	5002
55°	2836
60°	1627
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P225013

CATALOG NUMBER: LD2B10D010 EU2B10FL409040 2LBD*WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	171.9	20.9
10°-20°	343.9	41.8
20°-30°	217.4	26.5
30°-40°	68.0	8.3
40°-50°	15.8	1.9
50°-60°	4.2	0.5
60°-70°	0.8	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	733.2	89.2
0°-40°	801.2	97.5
0°-60°	821.2	99.9
0°-90°	821.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	821.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1925	
5°	1879	172
15°	1268	344
25°	465	217
35°	99	68
45°	18	16
55°	4	4
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P225013

CATALOG NUMBER: LD2B10D010 EU2B10FL409040 2LBD*WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1925.4
2.5°	1916.1
5°	1878.6
7.5°	1790.0
10°	1645.2
12.5°	1473.3
15°	1268.0
17.5°	1044.0
20°	829.4
22.5°	631.4
25°	464.7
27.5°	328.2
30°	221.9
32.5°	148.0
35°	99.0
37.5°	66.7
40°	43.8
42.5°	27.1
45°	17.7
47.5°	12.5
50°	8.3
52.5°	6.3
55°	4.2
57.5°	3.1
60°	2.1
62.5°	2.1
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)