

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P225298

Luminaire Tested: **LD2B10D010 EU2B10FL409040 2LBDC\*MMS**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P225298  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14835)  
Test Lab: INNOVATION CENTER (G1)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD2B10D010 EU2B10FL409040 2LBDC\*MMS  
Description: 1000 Lumen, 2inch Portfolio LED Downlight  
FLOOD OPTIC  
CAST ROUND TRIM WITH MATTE METALLIC SILVER  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 879.2 lumens  
Efficiency: N/A  
Efficacy: 85.4 lumens/watt  
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59  
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 10.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P225298

CATALOG NUMBER: LD2B10D010 EU2B10FL409040 2LBDC\*MMS

### Luminous Intensity Polar Plot





TEST NUMBER: P225298

CATALOG NUMBER: LD2B10D010 EU2B10FL409040 2LBDC\*MMS

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95			
2	110	106	102	99	108	104	101	98	101	98	96	98	96	94	95	94	92	91			
3	105	100	96	93	104	99	95	92	96	93	90	94	91	89	92	90	88	86			
4	101	95	90	87	100	94	90	86	92	88	85	90	87	85	88	86	84	82			
5	98	91	86	82	96	90	85	82	88	84	81	86	83	80	85	82	80	79			
6	94	86	82	78	93	86	81	78	84	80	77	83	79	77	82	79	76	75			
7	90	83	78	74	89	82	77	74	81	77	74	80	76	73	79	76	73	72			
8	87	79	74	71	86	79	74	71	78	74	71	77	73	70	76	73	70	69			
9	84	76	71	68	83	76	71	68	75	71	68	74	70	67	73	70	67	66			
10	81	73	68	65	80	73	68	65	72	68	65	71	68	65	71	67	65	64			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	795957
5°	781462
10°	694684
15°	546336
20°	363565
25°	208694
30°	105421
35°	49603
40°	19973
45°	9860
50°	5423
55°	3782
60°	3486
65°	2108
70°	2605
75°	1646
80°	2454
85°	0



TEST NUMBER: P225298

CATALOG NUMBER: LD2B10D010 EU2B10FL409040 2LBDC\*MMS

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	184.1	20.9
10°-20°	369.0	42.0
20°-30°	229.6	26.1
30°-40°	70.6	8.0
40°-50°	15.5	1.8
50°-60°	5.5	0.6
60°-70°	2.8	0.3
70°-80°	1.6	0.2
80°-90°	0.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	782.7	89.0
0°-40°	853.3	97.1
0°-60°	874.3	99.4
0°-90°	879.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	879.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2055	
5°	2010	184
15°	1362	369
25°	488	230
35°	105	71
45°	18	16
55°	6	6
65°	2	3
75°	1	2
85°	0	0
90°	0	



TEST NUMBER: P225298

CATALOG NUMBER: LD2B10D010 EU2B10FL409040 2LBDC\*MMS

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2054.9
2.5°	2045.9
5°	2009.8
7.5°	1918.4
10°	1766.2
12.5°	1583.5
15°	1362.4
17.5°	1121.0
20°	882.0
22.5°	668.8
25°	488.3
27.5°	344.0
30°	235.7
32.5°	159.0
35°	104.9
37.5°	63.2
40°	39.5
42.5°	27.1
45°	18.0
47.5°	12.4
50°	9.0
52.5°	7.9
55°	5.6
57.5°	4.5
60°	4.5
62.5°	3.4
65°	2.3
67.5°	2.3
70°	2.3
72.5°	2.3
75°	1.1
77.5°	1.1
80°	1.1
82.5°	1.1
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)