

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P264829

Luminaire Tested: **LD2B15D010 EU2B1510SP158050 2LBLC*MB**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P264829
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1711-432-2)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B15D010 EU2B1510SP158050 2LBLC*MB
Description: 1500 Lumen, 2inch Portfolio LED Downlight
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1209.0 lumens
Efficiency: N/A
Efficacy: 84.5 lumens/watt
Spacing Criteria (0/90/45): 0.31 / 0.31 / 0.32
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P264829

CATALOG NUMBER: LD2B15D010 EU2B1510SP158050 2LBLC*MB

Luminous Intensity Polar Plot





TEST NUMBER: P264829

CATALOG NUMBER: LD2B15D010 EU2B1510SP158050 2LBLC*MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	115	113	111	110	113	111	110	108	107	106	105	104	103	102	100	99	99	97	97	97	97
2	112	108	106	103	110	107	104	102	104	102	100	101	99	98	98	97	96	94	94	94	94
3	109	104	101	98	107	103	100	97	100	98	96	98	96	94	96	94	93	92	92	92	92
4	105	100	97	94	104	99	96	93	97	95	92	96	93	91	94	92	90	89	89	89	89
5	103	97	93	91	101	96	93	90	95	92	89	93	91	89	92	90	88	87	87	87	87
6	100	94	90	88	99	94	90	87	92	89	87	91	88	86	90	88	86	85	85	85	85
7	98	92	88	85	97	91	88	85	90	87	85	89	86	84	88	86	84	83	83	83	83
8	95	89	86	83	94	89	85	83	88	85	82	87	84	82	86	84	82	81	81	81	81
9	93	87	83	81	92	87	83	81	86	83	81	85	82	80	85	82	80	79	79	79	79
10	91	85	82	79	91	85	81	79	84	81	79	84	81	79	83	80	78	78	78	78	78

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	4268023
5°	3473757
10°	1876443
15°	748170
20°	299999
25°	143658
30°	74458
35°	39389
40°	21833
45°	13536
50°	9287
55°	6279
60°	4736
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P264829

CATALOG NUMBER: LD2B15D010 EU2B1510SP158050 2LBLC*MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	564.1	46.7
10°-20°	445.1	36.8
20°-30°	131.3	10.9
30°-40°	43.7	3.6
40°-50°	16.4	1.4
50°-60°	7.3	0.6
60°-70°	1.2	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1140.4	94.3
0°-40°	1184.1	97.9
0°-60°	1207.8	99.9
0°-90°	1209.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1209.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8651	
5°	7014	564
15°	1465	445
25°	264	131
35°	65	44
45°	19	16
55°	7	7
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P264829

CATALOG NUMBER: LD2B15D010 EU2B1510SP158050 2LBLC*MB

CANDELA DISTRIBUTION (FULL):

0°	
0°	8650.9
2.5°	8302.2
5°	7014.2
7.5°	5404.1
10°	3745.6
12.5°	2397.0
15°	1464.8
17.5°	893.4
20°	571.4
22.5°	382.5
25°	263.9
27.5°	186.4
30°	130.7
32.5°	92.0
35°	65.4
37.5°	46.0
40°	33.9
42.5°	26.6
45°	19.4
47.5°	16.9
50°	12.1
52.5°	9.7
55°	7.3
57.5°	7.3
60°	4.8
62.5°	2.4
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)