

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P264813

Luminaire Tested: **LD2B10D010 EU2B1010SP158050 2LBDL\*WH**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P264813  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1711-432-2)  
Test Lab: INNOVATION CENTER(G3)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD2B10D010 EU2B1010SP158050 2LBDL\*WH  
Description: 1000 Lumen, 2inch Portfolio LED Downlight  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1041.0 lumens  
Efficiency: N/A  
Efficacy: 101.1 lumens/watt  
Spacing Criteria (0/90/45): 0.31 / 0.31 / 0.32  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 10.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P264813

CATALOG NUMBER: LD2B10D010 EU2B1010SP158050 2LBDL\*WH

### Luminous Intensity Polar Plot





TEST NUMBER: P264813

CATALOG NUMBER: LD2B10D010 EU2B1010SP158050 2LBDL\*WH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	113	111	110	113	111	110	108	107	106	105	104	103	102	100	99	99	97
2	112	108	106	103	110	107	104	102	104	102	100	101	99	98	98	97	96	94
3	109	104	101	98	107	103	100	97	100	98	96	98	96	94	96	94	93	92
4	105	100	97	94	104	99	96	93	97	95	92	96	93	91	94	92	90	89
5	103	97	93	91	101	96	93	90	95	92	89	93	91	89	92	90	88	87
6	100	94	90	88	99	94	90	87	92	89	87	91	88	86	90	88	86	85
7	98	92	88	85	97	91	88	85	90	87	85	89	86	84	88	86	84	83
8	95	89	86	83	94	89	85	83	88	85	82	87	84	82	86	84	82	81
9	93	87	83	81	92	87	83	81	86	83	81	85	82	80	85	82	80	79
10	91	85	82	79	91	85	81	79	84	81	79	84	81	79	83	80	78	78

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	3674953
5°	2991040
10°	1615687
15°	644229
20°	258312
25°	123680
30°	64147
35°	33909
40°	18806
45°	11652
50°	7982
55°	5419
60°	4144
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P264813

CATALOG NUMBER: LD2B10D010 EU2B1010SP158050 2LBDL\*WH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	485.7	46.7
10°-20°	383.2	36.8
20°-30°	113.0	10.9
30°-40°	37.6	3.6
40°-50°	14.1	1.4
50°-60°	6.3	0.6
60°-70°	1.0	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	982.0	94.3
0°-40°	1019.6	97.9
0°-60°	1040.0	99.9
0°-90°	1041.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1041.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	7449	
5°	6040	486
15°	1261	383
25°	227	113
35°	56	38
45°	17	14
55°	6	6
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P264813

CATALOG NUMBER: LD2B10D010 EU2B1010SP158050 2LBDL\*WH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	7448.8
2.5°	7148.6
5°	6039.5
7.5°	4653.1
10°	3225.1
12.5°	2063.9
15°	1261.3
17.5°	769.3
20°	492.0
22.5°	329.4
25°	227.2
27.5°	160.5
30°	112.6
32.5°	79.2
35°	56.3
37.5°	39.6
40°	29.2
42.5°	22.9
45°	16.7
47.5°	14.6
50°	10.4
52.5°	8.3
55°	6.3
57.5°	6.3
60°	4.2
62.5°	2.1
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)