

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P263963

Luminaire Tested: **LD2B20D010 EU2B2010SP158027 2LBSQC*MMS**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P263963
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1805-787-1)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B20D010 EU2B2010SP158027 2LBSQC*MMS
Description: 2000 Lumen, 2inch Portfolio LED Downlight
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1789.0 lumens
Efficiency: N/A
Efficacy: 85.6 lumens/watt
Spacing Criteria (0/90/45): 0.28 / 0.28 / 0.28
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P263963

CATALOG NUMBER: LD2B20D010 EU2B2010SP158027 2LBSQC*MMS

Luminous Intensity Polar Plot





TEST NUMBER: P263963

CATALOG NUMBER: LD2B20D010 EU2B2010SP158027 2LBSQC*MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																			
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																												
1	116	114	112	111	113	112	110	109	108	107	106	104	103	102	101	100	100	98	97	96	95	94	93	92	91	90	89																			
2	113	109	107	105	111	108	106	104	105	103	101	102	101	99	99	98	97	96	95	94	93	92	91	90	89	88	87																			
3	110	106	103	100	108	105	102	100	102	100	98	100	98	97	98	96	95	94	93	92	91	90	89	88	87	86	85																			
4	107	103	99	97	106	102	99	96	100	97	95	98	96	94	96	95	93	92	91	90	89	88	87	86	85	84	83																			
5	105	100	97	94	104	99	96	94	98	95	93	96	94	92	95	93	91	90	89	88	87	86	85	84	83	82	81																			
6	103	98	94	92	102	97	94	91	96	93	91	95	92	90	93	91	90	89	88	87	86	85	84	83	82	81	80																			
7	101	95	92	90	100	95	92	89	94	91	89	93	90	89	92	90	88	87	86	85	84	83	82	81	80	79	78																			
8	99	93	90	88	98	93	90	88	92	89	87	91	89	87	91	88	87	86	85	84	83	82	81	80	79	78	77																			
9	97	92	88	86	96	91	88	86	91	88	86	90	87	86	89	87	85	84	83	82	81	80	79	78	77	76	75																			
10	95	90	87	85	95	90	87	85	89	86	85	89	86	84	88	86	84	83	82	81	80	79	78	77	76	75	74																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	8441618
5°	6766353
10°	2953234
15°	915190
20°	319057
25°	140936
30°	63805
35°	33186
40°	18935
45°	9001
50°	5603
55°	3183
60°	1776
65°	2101
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P263963

CATALOG NUMBER: LD2B20D010 EU2B2010SP158027 2LBSQC*MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1037.5	58.0
10°-20°	568.2	31.8
20°-30°	129.5	7.2
30°-40°	37.2	2.1
40°-50°	11.5	0.6
50°-60°	3.4	0.2
60°-70°	1.6	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1735.2	97.0
0°-40°	1772.5	99.1
0°-60°	1787.4	99.9
0°-90°	1789.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1789.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	17110	
5°	13663	###
15°	1792	568
25°	259	130
35°	55	37
45°	13	12
55°	4	3
65°	2	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P263963

CATALOG NUMBER: LD2B20D010 EU2B2010SP158027 2LBSQC*MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	17110.4
1°	16897.4
2°	16454.9
3°	15768.3
4°	14824.7
5°	13662.6
6°	12237.9
7°	10646.2
8°	8984.8
9°	7376.5
10°	5895.0
11°	4641.1
12°	3653.4
13°	2875.0
14°	2271.0
15°	1791.8
16°	1413.6
17°	1125.4
18°	905.1
19°	736.2
20°	607.7
22.5°	392.9
25°	258.9
26°	218.5
27°	185.4
28°	156.0
29°	130.3
30°	112.0
32.5°	77.1
35°	55.1
37.5°	40.4
40°	29.4
42.5°	20.2
45°	12.9
47.5°	9.2
50°	7.3
52.5°	5.5
55°	3.7
57.5°	1.8
60°	1.8
62.5°	1.8
65°	1.8
67.5°	1.8



TEST NUMBER: P263963

CATALOG NUMBER: LD2B20D010 EU2B2010SP158027 2LBSQC*MMS

CANDELA DISTRIBUTION (continued):

	0°
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







70°		0.0
72.5°		0.0



(END OF REPORT)