

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224487

Luminaire Tested: **LD2B20D010 EU2B20FL408027 2LBDL*WH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P224487
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14831)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B20D010 EU2B20FL408027 2LBDL*WH
Description: 2000 Lumen, 2inch Portfolio LED Downlight
FLOOD OPTIC
LENSED SPUN ROUND TRIM WITH WHEAT HAZE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1752.7 lumens
Efficiency: N/A
Efficacy: 83.9 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P224487

CATALOG NUMBER: LD2B20D010 EU2B20FL408027 2LBDL*WH

Luminous Intensity Polar Plot





TEST NUMBER: P224487

CATALOG NUMBER: LD2B20D010 EU2B20FL408027 2LBDL*WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | | | 0 | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | 100 | 100 | 100 |
| 1 | 114 | 112 | 110 | 108 | 112 | 110 | 108 | 106 | 106 | 104 | 103 | 102 | 101 | 100 | 99 | 98 | 97 | 95 | 95 | 95 | 95 |
| 2 | 110 | 106 | 102 | 100 | 108 | 104 | 101 | 98 | 101 | 98 | 96 | 98 | 96 | 94 | 95 | 94 | 92 | 91 | 91 | 91 | 91 |
| 3 | 106 | 100 | 96 | 93 | 104 | 99 | 95 | 92 | 96 | 93 | 91 | 94 | 91 | 89 | 92 | 90 | 88 | 87 | 87 | 87 | 87 |
| 4 | 102 | 95 | 91 | 87 | 100 | 94 | 90 | 87 | 92 | 89 | 86 | 90 | 87 | 85 | 88 | 86 | 84 | 82 | 82 | 82 | 82 |
| 5 | 98 | 91 | 86 | 82 | 96 | 90 | 85 | 82 | 88 | 84 | 81 | 87 | 83 | 81 | 85 | 82 | 80 | 79 | 79 | 79 | 79 |
| 6 | 94 | 87 | 82 | 78 | 93 | 86 | 81 | 78 | 85 | 80 | 77 | 83 | 80 | 77 | 82 | 79 | 76 | 75 | 75 | 75 | 75 |
| 7 | 91 | 83 | 78 | 75 | 89 | 82 | 78 | 74 | 81 | 77 | 74 | 80 | 76 | 74 | 79 | 76 | 73 | 72 | 72 | 72 | 72 |
| 8 | 87 | 79 | 75 | 71 | 86 | 79 | 74 | 71 | 78 | 74 | 71 | 77 | 73 | 70 | 76 | 73 | 70 | 69 | 69 | 69 | 69 |
| 9 | 84 | 76 | 71 | 68 | 83 | 76 | 71 | 68 | 75 | 71 | 68 | 74 | 70 | 68 | 73 | 70 | 67 | 66 | 66 | 66 | 66 |
| 10 | 81 | 73 | 69 | 65 | 80 | 73 | 68 | 65 | 72 | 68 | 65 | 71 | 68 | 65 | 71 | 67 | 65 | 64 | 64 | 64 | 64 |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|---------|
| | 0° |
| 0° | 1617169 |
| 5° | 1556002 |
| 10° | 1369585 |
| 15° | 1075790 |
| 20° | 731417 |
| 25° | 427090 |
| 30° | 217507 |
| 35° | 102895 |
| 40° | 44901 |
| 45° | 19447 |
| 50° | 9340 |
| 55° | 6010 |
| 60° | 3409 |
| 65° | 0 |
| 70° | 0 |
| 75° | 0 |
| 80° | 0 |
| 85° | 0 |



TEST NUMBER: P224487

CATALOG NUMBER: LD2B20D010 EU2B20FL408027 2LBDL*WH

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 365.5 | 20.9 |
| 10°-20° | 729.5 | 41.6 |
| 20°-30° | 468.3 | 26.7 |
| 30°-40° | 148.6 | 8.5 |
| 40°-50° | 31.7 | 1.8 |
| 50°-60° | 8.1 | 0.5 |
| 60°-70° | 1.1 | 0.1 |
| 70°-80° | 0.0 | 0.0 |
| 80°-90° | 0.0 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 1563.2 | 89.2 |
| 0°-40° | 1711.8 | 97.7 |
| 0°-60° | 1751.6 | 99.9 |
| 0°-90° | 1752.7 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 1752.7 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 4175 | |
| 5° | 4002 | 365 |
| 15° | 2683 | 729 |
| 25° | 999 | 468 |
| 35° | 218 | 149 |
| 45° | 36 | 32 |
| 55° | 9 | 8 |
| 65° | 0 | 1 |
| 75° | 0 | 0 |
| 85° | 0 | 0 |
| 90° | 0 | |



TEST NUMBER: P224487

CATALOG NUMBER: LD2B20D010 EU2B20FL408027 2LBDL*WH

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|--------|
| 0° | 4175.0 |
| 2.5° | 4135.0 |
| 5° | 4001.8 |
| 7.5° | 3784.2 |
| 10° | 3482.1 |
| 12.5° | 3113.5 |
| 15° | 2682.7 |
| 17.5° | 2223.0 |
| 20° | 1774.4 |
| 22.5° | 1354.7 |
| 25° | 999.3 |
| 27.5° | 712.9 |
| 30° | 486.3 |
| 32.5° | 326.5 |
| 35° | 217.6 |
| 37.5° | 144.3 |
| 40° | 88.8 |
| 42.5° | 55.5 |
| 45° | 35.5 |
| 47.5° | 24.4 |
| 50° | 15.5 |
| 52.5° | 11.1 |
| 55° | 8.9 |
| 57.5° | 6.7 |
| 60° | 4.4 |
| 62.5° | 2.2 |
| 65° | 0.0 |
| 67.5° | 0.0 |
| 70° | 0.0 |
| 72.5° | 0.0 |
| 75° | 0.0 |
| 77.5° | 0.0 |
| 80° | 0.0 |
| 82.5° | 0.0 |
| 85° | 0.0 |
| 87.5° | 0.0 |
| 90° | 0.0 |



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)