

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P225325

Luminaire Tested: **LD2B10D010 EU2B10FL409050 2LBDC\*MW**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P225325  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14835)  
Test Lab: INNOVATION CENTER (G1)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD2B10D010 EU2B10FL409050 2LBDC\*MW  
Description: 1000 Lumen, 2inch Portfolio LED Downlight  
FLOOD OPTIC  
CAST ROUND TRIM WITH MATTE WHITE FINISH  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 784.5 lumens  
Efficiency: N/A  
Efficacy: 76.2 lumens/watt  
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59  
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 10.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P225325

CATALOG NUMBER: LD2B10D010 EU2B10FL409050 2LBDC\*MW

### Luminous Intensity Polar Plot





TEST NUMBER: P225325

CATALOG NUMBER: LD2B10D010 EU2B10FL409050 2LBDC\*MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |   |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|---|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |    |    |   |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |     | 30  |     |     |     | 10  |     |    | 0  |   |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30 | 10 | 0 |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |   |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |    |    |   |
| 1   | 114 | 112 | 110 | 108 | 112 | 110 | 108 | 106 | 106 | 104 | 103 | 102 | 101 | 100 | 99  | 98  | 97  | 95  |    |    |   |
| 2   | 110 | 106 | 102 | 99  | 108 | 104 | 101 | 98  | 101 | 98  | 96  | 98  | 96  | 94  | 95  | 94  | 92  | 91  |    |    |   |
| 3   | 105 | 100 | 96  | 93  | 104 | 99  | 95  | 92  | 96  | 93  | 90  | 94  | 91  | 89  | 92  | 90  | 88  | 86  |    |    |   |
| 4   | 101 | 95  | 90  | 87  | 100 | 94  | 90  | 86  | 92  | 88  | 85  | 90  | 87  | 85  | 88  | 86  | 84  | 82  |    |    |   |
| 5   | 98  | 91  | 86  | 82  | 96  | 90  | 85  | 82  | 88  | 84  | 81  | 86  | 83  | 80  | 85  | 82  | 80  | 79  |    |    |   |
| 6   | 94  | 87  | 82  | 78  | 93  | 86  | 81  | 78  | 84  | 80  | 77  | 83  | 80  | 77  | 82  | 79  | 76  | 75  |    |    |   |
| 7   | 90  | 83  | 78  | 74  | 89  | 82  | 77  | 74  | 81  | 77  | 74  | 80  | 76  | 73  | 79  | 76  | 73  | 72  |    |    |   |
| 8   | 87  | 79  | 74  | 71  | 86  | 79  | 74  | 71  | 78  | 74  | 71  | 77  | 73  | 70  | 76  | 73  | 70  | 69  |    |    |   |
| 9   | 84  | 76  | 71  | 68  | 83  | 76  | 71  | 68  | 75  | 71  | 68  | 74  | 70  | 67  | 73  | 70  | 67  | 66  |    |    |   |
| 10  | 81  | 73  | 68  | 65  | 80  | 73  | 68  | 65  | 72  | 68  | 65  | 71  | 68  | 65  | 71  | 67  | 65  | 64  |    |    |   |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 710199 |
| 5°  | 697281 |
| 10° | 619835 |
| 15° | 487508 |
| 20° | 324405 |
| 25° | 186213 |
| 30° | 94061  |
| 35° | 44260  |
| 40° | 17799  |
| 45° | 8819   |
| 50° | 4881   |
| 55° | 3377   |
| 60° | 3099   |
| 65° | 1833   |
| 70° | 2265   |
| 75° | 1497   |
| 80° | 2231   |
| 85° | 0      |



TEST NUMBER: P225325

CATALOG NUMBER: LD2B10D010 EU2B10FL409050 2LBDC\*MW

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 164.2  | 20.9      |
| 10°-20°   | 329.3  | 42.0      |
| 20°-30°   | 204.9  | 26.1      |
| 30°-40°   | 63.0   | 8.0       |
| 40°-50°   | 13.9   | 1.8       |
| 50°-60°   | 4.9    | 0.6       |
| 60°-70°   | 2.5    | 0.3       |
| 70°-80°   | 1.4    | 0.2       |
| 80°-90°   | 0.4    | 0.1       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 698.4  | 89.0      |
| 0°-40°    | 761.4  | 97.1      |
| 0°-60°    | 780.2  | 99.4      |
| 0°-90°    | 784.5  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 784.5  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 1834 |      |
| 5°  | 1793 | 164  |
| 15° | 1216 | 329  |
| 25° | 436  | 205  |
| 35° | 94   | 63   |
| 45° | 16   | 14   |
| 55° | 5    | 5    |
| 65° | 2    | 2    |
| 75° | 1    | 1    |
| 85° | 0    | 0    |
| 90° | 0    |      |



TEST NUMBER: P225325

CATALOG NUMBER: LD2B10D010 EU2B10FL409050 2LBDC\*MW

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     |
|-------|--------|
| 0°    | 1833.5 |
| 2.5°  | 1825.5 |
| 5°    | 1793.3 |
| 7.5°  | 1711.8 |
| 10°   | 1575.9 |
| 12.5° | 1412.9 |
| 15°   | 1215.7 |
| 17.5° | 1000.3 |
| 20°   | 787.0  |
| 22.5° | 596.8  |
| 25°   | 435.7  |
| 27.5° | 306.9  |
| 30°   | 210.3  |
| 32.5° | 141.9  |
| 35°   | 93.6   |
| 37.5° | 56.4   |
| 40°   | 35.2   |
| 42.5° | 24.2   |
| 45°   | 16.1   |
| 47.5° | 11.1   |
| 50°   | 8.1    |
| 52.5° | 7.0    |
| 55°   | 5.0    |
| 57.5° | 4.0    |
| 60°   | 4.0    |
| 62.5° | 3.0    |
| 65°   | 2.0    |
| 67.5° | 2.0    |
| 70°   | 2.0    |
| 72.5° | 2.0    |
| 75°   | 1.0    |
| 77.5° | 1.0    |
| 80°   | 1.0    |
| 82.5° | 1.0    |
| 85°   | 0.0    |
| 87.5° | 0.0    |
| 90°   | 0.0    |



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)