

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224927

Luminaire Tested: **LD2B20D010 EU2B20FL409027 2LBD\*H**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P224927  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (156)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD2B20D010 EU2B20FL409027 2LBD\*H  
Description: 2000 Lumen, 2inch Portfolio LED Downlight  
FLOOD OPTIC  
SPUN ROUND TRIM WITH HAZE FINISH  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1434.2 lumens  
Efficiency: N/A  
Efficacy: 68.6 lumens/watt  
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.59  
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 20.9  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P224927

CATALOG NUMBER: LD2B20D010 EU2B20FL409027 2LBD\*H

### Luminous Intensity Polar Plot





TEST NUMBER: P224927

CATALOG NUMBER: LD2B20D010 EU2B20FL409027 2LBD\*H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95			95
2	110	106	103	100	108	104	101	99	101	99	97	98	96	94	96	94	93	91			91
3	106	100	96	93	104	99	95	92	97	94	91	94	92	90	92	90	88	87			87
4	102	96	91	88	100	94	90	87	92	89	86	91	88	85	89	86	84	83			83
5	98	91	86	83	96	90	86	82	89	85	82	87	84	81	86	83	80	79			79
6	94	87	82	79	93	86	82	78	85	81	78	84	80	77	82	79	77	76			76
7	91	83	78	75	90	83	78	75	82	77	74	80	77	74	79	76	74	73			73
8	88	80	75	72	87	79	75	72	78	74	71	77	74	71	77	73	71	70			70
9	85	77	72	69	84	76	72	69	75	71	68	75	71	68	74	70	68	67			67
10	82	74	69	66	81	73	69	66	73	69	66	72	68	66	71	68	65	64			64

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1330262
5°	1302410
10°	1147043
15°	899947
20°	597615
25°	343065
30°	172064
35°	79441
40°	32311
45°	14462
50°	7533
55°	4660
60°	2169
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P224927

CATALOG NUMBER: LD2B20D010 EU2B20FL409027 2LBD\*H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	305.9	21.3
10°-20°	607.4	42.4
20°-30°	377.4	26.3
30°-40°	113.8	7.9
40°-50°	23.3	1.6
50°-60°	6.0	0.4
60°-70°	0.3	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1290.8	90.0
0°-40°	1404.6	97.9
0°-60°	1433.9	100.0
0°-90°	1434.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1434.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3434	
5°	3350	306
15°	2244	607
25°	803	377
35°	168	114
45°	26	23
55°	7	6
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P224927

CATALOG NUMBER: LD2B20D010 EU2B20FL409027 2LBD\*H

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3434.3
1°	3423.2
2°	3408.0
3°	3396.8
4°	3380.2
5°	3349.6
6°	3301.0
7°	3234.4
8°	3138.5
9°	3030.2
10°	2916.3
11°	2795.5
12°	2669.1
13°	2537.2
14°	2392.8
15°	2244.2
17.5°	1845.6
20°	1449.8
22.5°	1099.9
25°	802.7
27.5°	566.6
30°	384.7
32.5°	252.7
35°	168.0
37.5°	104.2
40°	63.9
42.5°	41.7
45°	26.4
47.5°	16.7
50°	12.5
52.5°	8.3
55°	6.9
57.5°	4.2
60°	2.8
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P224927

CATALOG NUMBER: LD2B20D010 EU2B20FL409027 2LBD\*H

**CANDELA DISTRIBUTION (continued):**

0°  
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)