

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P#

Luminaire Tested: **LD2B10D010 EU2B10WFL559050 2LBDLC\*MW**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P#  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14810)  
Test Lab: INNOVATION CENTER (G1)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD2B10D010 EU2B10WFL559050 2LBDLC\*MW  
Description: 1000 Lumen, 2inch Portfolio LED Downlight  
WIDE FLOOD OPTIC  
LENSED CAST ROUND TRIM WITH MATTE WHITE FINISH  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 768.6 lumens  
Efficiency: N/A  
Efficacy: 74.6 lumens/watt  
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.84  
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 10.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P#

CATALOG NUMBER: LD2B10D010 EU2B10WFL559050 2LBDLC\**MW*

### Luminous Intensity Polar Plot





TEST NUMBER: P#

CATALOG NUMBER: LD2B10D010 EU2B10WFL559050 2LBDLC\*MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	108	106	111	108	106	104	104	102	101	101	99	98	97	96	95	93				93
2	108	102	98	95	105	101	97	94	98	94	92	95	92	90	92	90	88	86				86
3	102	95	90	86	100	94	89	85	91	87	84	89	85	83	87	84	81	80				80
4	97	89	83	79	95	88	82	78	85	81	77	83	80	76	82	78	76	74				74
5	91	83	77	72	90	82	76	72	80	75	71	78	74	71	77	73	70	69				69
6	87	78	71	67	85	77	71	67	75	70	66	74	69	66	73	69	65	64				64
7	82	73	67	62	81	72	66	62	71	66	62	70	65	62	69	64	61	60				60
8	78	69	62	58	77	68	62	58	67	62	58	66	61	58	65	61	57	56				56
9	74	65	59	55	73	64	58	54	63	58	54	62	57	54	61	57	54	52				52
10	71	61	55	51	70	61	55	51	60	55	51	59	54	51	58	54	51	49				49

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	360503
5°	358186
10°	332986
15°	292336
20°	251981
25°	215490
30°	171036
35°	119209
40°	75442
45°	46014
50°	27238
55°	14925
60°	3254
65°	2933
70°	2378
75°	3143
80°	2454
85°	4889



TEST NUMBER: P#

CATALOG NUMBER: LD2B10D010 EU2B10WFL559050 2LBDLC\*MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	85.5	11.1
10°-20°	203.0	26.4
20°-30°	229.1	29.8
30°-40°	158.5	20.6
40°-50°	67.5	8.8
50°-60°	19.6	2.5
60°-70°	2.9	0.4
70°-80°	1.8	0.2
80°-90°	0.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	517.6	67.3
0°-40°	676.1	88.0
0°-60°	763.2	99.3
0°-90°	768.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	768.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	931	
5°	921	85
15°	729	203
25°	504	229
35°	252	158
45°	84	68
55°	22	20
65°	3	3
75°	2	2
85°	1	1
90°	0	



TEST NUMBER: P#

CATALOG NUMBER: LD2B10D010 EU2B10WFL559050 2LBDLC\*MW

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	930.7
2.5°	929.6
5°	921.2
7.5°	892.9
10°	846.6
12.5°	789.9
15°	729.0
17.5°	666.0
20°	611.3
22.5°	559.9
25°	504.2
27.5°	445.4
30°	382.4
32.5°	314.1
35°	252.1
37.5°	195.4
40°	149.2
42.5°	112.4
45°	84.0
47.5°	60.9
50°	45.2
52.5°	32.6
55°	22.1
57.5°	9.5
60°	4.2
62.5°	3.2
65°	3.2
67.5°	2.1
70°	2.1
72.5°	2.1
75°	2.1
77.5°	1.1
80°	1.1
82.5°	1.1
85°	1.1
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)