

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P264970

Luminaire Tested: **LD2B10D010 EU2B1010SP159030D2W 2LBDL*WMH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P264970
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1711-432-2)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B10D010 EU2B1010SP159030D2W 2LBDL*WMH
Description: 1000 Lumen, 2inch Portfolio LED Downlight
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 544.6 lumens
Efficiency: N/A
Efficacy: 52.9 lumens/watt
Spacing Criteria (0/90/45): 0.31 / 0.31 / 0.32
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P264970

CATALOG NUMBER: LD2B10D010 EU2B1010SP159030D2W 2LBDL*WMH

Luminous Intensity Polar Plot





TEST NUMBER: P264970

CATALOG NUMBER: LD2B10D010 EU2B1010SP159030D2W 2LBDL*WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	113	111	110	113	111	110	108	107	106	105	104	103	102	100	99	99	97
2	112	108	106	103	110	107	104	102	104	102	100	101	99	98	98	97	96	94
3	109	104	101	98	107	103	100	97	100	98	96	98	96	94	96	94	93	92
4	106	100	97	94	104	99	96	93	97	95	92	96	93	91	94	92	90	89
5	103	97	93	91	101	96	93	90	95	92	89	93	91	89	92	90	88	87
6	100	94	90	88	99	94	90	87	92	89	87	91	88	86	90	88	86	85
7	98	92	88	85	97	91	88	85	90	87	85	89	86	84	88	86	84	83
8	95	89	86	83	94	89	85	83	88	85	82	87	84	82	86	84	82	81
9	93	87	83	81	92	87	83	81	86	83	81	85	82	80	85	82	80	79
10	91	85	82	79	91	85	81	79	84	81	79	84	81	79	83	80	78	78

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1922680
5°	1564879
10°	845291
15°	337054
20°	135141
25°	64725
30°	33554
35°	17767
40°	9789
45°	6070
50°	4221
55°	2838
60°	2072
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P264970

CATALOG NUMBER: LD2B10D010 EU2B1010SP159030D2W 2LBDL*WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	254.1	46.7
10°-20°	200.5	36.8
20°-30°	59.1	10.9
30°-40°	19.7	3.6
40°-50°	7.4	1.4
50°-60°	3.3	0.6
60°-70°	0.5	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	513.7	94.3
0°-40°	533.4	97.9
0°-60°	544.1	99.9
0°-90°	544.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	544.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3897	
5°	3160	254
15°	660	200
25°	119	59
35°	30	20
45°	9	7
55°	3	3
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P264970

CATALOG NUMBER: LD2B10D010 EU2B1010SP159030D2W 2LBDL*WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	3897.1
2.5°	3740.0
5°	3159.8
7.5°	2434.5
10°	1687.3
12.5°	1079.8
15°	659.9
17.5°	402.5
20°	257.4
22.5°	172.3
25°	118.9
27.5°	84.0
30°	58.9
32.5°	41.4
35°	29.5
37.5°	20.7
40°	15.2
42.5°	12.0
45°	8.7
47.5°	7.6
50°	5.5
52.5°	4.4
55°	3.3
57.5°	3.3
60°	2.1
62.5°	1.1
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)