

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P264529

Luminaire Tested: **LD2B20D010 EU2B2010SP159727 2LBD*B**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P264529
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1805-787-1)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B20D010 EU2B2010SP159727 2LBD*B
Description: 2000 Lumen, 2inch Portfolio LED Downlight
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1217.9 lumens
Efficiency: N/A
Efficacy: 58.3 lumens/watt
Spacing Criteria (0/90/45): 0.28 / 0.28 / 0.28
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P264529

CATALOG NUMBER: LD2B20D010 EU2B2010SP159727 2LBD*B

Luminous Intensity Polar Plot





TEST NUMBER: P264529

CATALOG NUMBER: LD2B20D010 EU2B2010SP159727 2LBD*B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	116	114	112	111	113	112	110	109	108	107	106	104	103	102	101	100	100	98				98
2	113	109	107	105	111	108	106	104	105	103	101	102	101	99	99	98	97	96				96
3	110	106	103	100	108	105	102	100	102	100	98	100	98	97	98	96	95	94				94
4	107	103	99	97	106	102	99	96	100	97	95	98	96	94	96	95	93	92				92
5	105	100	97	94	104	99	96	94	98	95	93	96	94	92	95	93	91	90				90
6	103	98	94	92	102	97	94	91	96	93	91	95	92	90	93	91	90	89				89
7	101	95	92	90	100	95	92	89	94	91	89	93	90	89	92	90	88	87				87
8	99	93	90	88	98	93	90	88	92	89	87	91	89	87	91	88	87	86				86
9	97	92	88	86	96	91	88	86	91	88	86	90	87	86	89	87	85	85				85
10	95	90	87	85	95	90	87	85	89	86	85	89	86	84	88	86	84	83				83

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	5747270
5°	4606732
10°	2010654
15°	623083
20°	217203
25°	95917
30°	43410
35°	22586
40°	12881
45°	6070
50°	3838
55°	2150
60°	1184
65°	1401
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P264529

CATALOG NUMBER: LD2B20D010 EU2B2010SP159727 2LBD*B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	706.4	58.0
10°-20°	386.8	31.8
20°-30°	88.2	7.2
30°-40°	25.3	2.1
40°-50°	7.8	0.6
50°-60°	2.3	0.2
60°-70°	1.0	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1181.4	97.0
0°-40°	1206.7	99.1
0°-60°	1216.8	99.9
0°-90°	1217.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1217.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	11649	
5°	9302	706
15°	1220	387
25°	176	88
35°	38	25
45°	9	8
55°	2	2
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P264529

CATALOG NUMBER: LD2B20D010 EU2B2010SP159727 2LBD*B

CANDELA DISTRIBUTION (FULL):

	0°
0°	11649.2
1°	11504.2
2°	11203.0
3°	10735.5
4°	10093.1
5°	9301.9
6°	8331.9
7°	7248.2
8°	6117.1
9°	5022.2
10°	4013.5
11°	3159.8
12°	2487.3
13°	1957.4
14°	1546.1
15°	1219.9
16°	962.4
17°	766.2
18°	616.2
19°	501.2
20°	413.7
22.5°	267.5
25°	176.2
26°	148.7
27°	126.2
28°	106.2
29°	88.7
30°	76.2
32.5°	52.5
35°	37.5
37.5°	27.5
40°	20.0
42.5°	13.7
45°	8.7
47.5°	6.2
50°	5.0
52.5°	3.7
55°	2.5
57.5°	1.2
60°	1.2
62.5°	1.2
65°	1.2
67.5°	1.2



TEST NUMBER: P264529

CATALOG NUMBER: LD2B20D010 EU2B2010SP159727 2LBD*B

CANDELA DISTRIBUTION (continued):

	0°
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







70°		0.0
72.5°		0.0



(END OF REPORT)