

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224913

Luminaire Tested: **LD2B10D010 EU2B10FL409030D2W 2LBD\*H**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P224913  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (156)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD2B10D010 EU2B10FL409030D2W 2LBD\*H  
Description: 1000 Lumen, 2inch Portfolio LED Downlight  
FLOOD OPTIC  
SPUN ROUND TRIM WITH HAZE FINISH  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 610.1 lumens  
Efficiency: N/A  
Efficacy: 59.2 lumens/watt  
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.59  
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 10.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P224913

CATALOG NUMBER: LD2B10D010 EU2B10FL409030D2W 2LBD\*H

### Luminous Intensity Polar Plot





TEST NUMBER: P224913

CATALOG NUMBER: LD2B10D010 EU2B10FL409030D2W 2LBD\*H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95			95
2	110	106	103	100	108	104	101	99	101	99	97	98	96	94	96	94	93	91			91
3	106	100	96	93	104	99	95	92	97	93	91	94	92	90	92	90	88	87			87
4	102	96	91	88	100	94	90	87	92	89	86	91	88	85	89	86	84	83			83
5	98	91	86	83	96	90	86	82	89	85	82	87	84	81	86	83	80	79			79
6	94	87	82	79	93	86	82	78	85	81	78	84	80	77	82	79	77	76			76
7	91	83	78	75	90	83	78	75	82	77	74	80	77	74	79	76	74	73			73
8	88	80	75	72	87	79	75	72	78	74	71	77	74	71	77	73	71	70			70
9	85	77	72	69	84	76	72	69	75	71	68	75	71	68	74	70	68	67			67
10	82	74	69	66	81	73	69	66	73	69	66	72	68	66	71	68	65	64			64

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	565835
5°	553999
10°	487955
15°	382844
20°	254207
25°	145953
30°	73173
35°	33810
40°	13754
45°	6135
50°	3194
55°	2026
60°	930
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P224913

CATALOG NUMBER: LD2B10D010 EU2B10FL409030D2W 2LBD\*H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	130.1	21.3
10°-20°	258.4	42.3
20°-30°	160.5	26.3
30°-40°	48.4	7.9
40°-50°	9.9	1.6
50°-60°	2.6	0.4
60°-70°	0.1	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	549.1	90.0
0°-40°	597.5	97.9
0°-60°	610.0	100.0
0°-90°	610.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	610.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1461	
5°	1425	130
15°	955	258
25°	342	161
35°	72	48
45°	11	10
55°	3	3
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P224913

CATALOG NUMBER: LD2B10D010 EU2B10FL409030D2W 2LBD\*H

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1460.8
1°	1456.2
2°	1449.7
3°	1444.9
4°	1437.8
5°	1424.8
6°	1404.2
7°	1375.8
8°	1335.1
9°	1289.0
10°	1240.6
11°	1189.1
12°	1135.4
13°	1079.3
14°	1017.8
15°	954.7
17.5°	785.1
20°	616.7
22.5°	467.9
25°	341.5
27.5°	241.0
30°	163.6
32.5°	107.5
35°	71.5
37.5°	44.3
40°	27.2
42.5°	17.8
45°	11.2
47.5°	7.1
50°	5.3
52.5°	3.6
55°	3.0
57.5°	1.8
60°	1.2
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P224913

CATALOG NUMBER: LD2B10D010 EU2B10FL409030D2W 2LBD\*H

**CANDELA DISTRIBUTION (continued):**

0°  
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)