

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P265202

Luminaire Tested: **LD2B20D010 EU2B2010SP159727 2LBDL\*GPH**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P265202  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1711-432-2)  
Test Lab: INNOVATION CENTER(G3)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD2B20D010 EU2B2010SP159727 2LBDL\*GPH  
Description: 2000 Lumen, 2inch Portfolio LED Downlight  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1161.0 lumens  
Efficiency: N/A  
Efficacy: 55.6 lumens/watt  
Spacing Criteria (0/90/45): 0.31 / 0.31 / 0.32  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 20.9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P265202

CATALOG NUMBER: LD2B20D010 EU2B2010SP159727 2LBDL\*GPH

### Luminous Intensity Polar Plot





TEST NUMBER: P265202

CATALOG NUMBER: LD2B20D010 EU2B2010SP159727 2LBDL\*GPH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									20								
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR	0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100	100	100	100	100	100	100	100	100															
	1	115	113	111	110	113	111	110	108	107	106	105	104	103	102	100	99	99	97	97	97	97	97	97	97	97	97	97	97	97															
	2	112	108	106	103	110	107	104	102	104	102	100	101	99	98	98	97	96	94	94	94	94	94	94	94	94	94	94	94	94															
	3	109	104	101	98	107	103	100	97	100	98	96	98	96	94	96	94	93	92	92	92	92	92	92	92	92	92	92	92	92															
	4	105	100	97	94	104	99	96	93	97	95	92	96	93	91	94	92	90	89	89	89	89	89	89	89	89	89	89	89	89															
	5	103	97	93	91	101	96	93	90	95	92	89	93	91	89	92	90	88	87	87	87	87	87	87	87	87	87	87	87	87															
	6	100	94	90	88	99	94	90	87	92	89	87	91	88	86	90	88	86	85	85	85	85	85	85	85	85	85	85	85	85															
	7	98	92	88	85	97	91	88	85	90	87	85	89	86	84	88	86	84	83	83	83	83	83	83	83	83	83	83	83	83	83														
	8	95	89	86	83	94	89	85	83	88	85	82	87	84	82	86	84	82	81	81	81	81	81	81	81	81	81	81	81	81	81														
	9	93	87	83	81	92	87	83	81	86	83	81	85	82	80	85	82	80	79	79	79	79	79	79	79	79	79	79	79	79	79														
	10	91	85	82	79	91	85	81	79	84	81	79	84	81	79	83	80	78	78	78	78	78	78	78	78	78	78	78	78	78	78														

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	4098554
5°	3335831
10°	1801949
15°	718494
20°	288081
25°	137942
30°	71552
35°	37823
40°	20996
45°	12978
50°	8903
55°	6021
60°	4638
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P265202

CATALOG NUMBER: LD2B20D010 EU2B2010SP159727 2LBDL\*GPH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	541.7	46.7
10°-20°	427.4	36.8
20°-30°	126.1	10.9
30°-40°	42.0	3.6
40°-50°	15.8	1.4
50°-60°	7.0	0.6
60°-70°	1.1	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1095.1	94.3
0°-40°	1137.1	97.9
0°-60°	1159.9	99.9
0°-90°	1161.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1161.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	8307	
5°	6736	542
15°	1407	427
25°	253	126
35°	63	42
45°	19	16
55°	7	7
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P265202

CATALOG NUMBER: LD2B20D010 EU2B2010SP159727 2LBDL\*GPH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	8307.4
2.5°	7972.6
5°	6735.7
7.5°	5189.5
10°	3596.9
12.5°	2301.8
15°	1406.7
17.5°	857.9
20°	548.7
22.5°	367.4
25°	253.4
27.5°	179.0
30°	125.6
32.5°	88.4
35°	62.8
37.5°	44.2
40°	32.6
42.5°	25.6
45°	18.6
47.5°	16.3
50°	11.6
52.5°	9.3
55°	7.0
57.5°	7.0
60°	4.7
62.5°	2.3
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)