

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P225451

Luminaire Tested: **LD2B10D010 EU2B10FL409030D2W 2LBDLC*MB**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P225451
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14833)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B10D010 EU2B10FL409030D2W 2LBDLC*MB
Description: 1000 Lumen, 2inch Portfolio LED Downlight
FLOOD OPTIC
LENSED CAST ROUND TRIM WITH MATTE BLACK FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 558.8 lumens
Efficiency: N/A
Efficacy: 54.3 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.6
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P225451

CATALOG NUMBER: LD2B10D010 EU2B10FL409030D2W 2LBDLC*MB

Luminous Intensity Polar Plot





TEST NUMBER: P225451

CATALOG NUMBER: LD2B10D010 EU2B10FL409030D2W 2LBDLC*MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20																	
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																								
RCR																																																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																																				
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95																																				
2	110	105	102	99	107	104	101	98	101	98	96	98	96	94	95	93	92	90																																				
3	105	100	95	92	103	98	94	91	96	92	90	93	91	88	91	89	87	86																																				
4	101	94	90	86	99	93	89	86	91	87	85	89	86	84	88	85	83	81																																				
5	97	90	85	81	95	89	84	81	87	83	80	85	82	79	84	81	79	77																																				
6	93	85	80	77	92	85	80	76	83	79	76	82	78	75	81	77	75	74																																				
7	89	81	76	73	88	81	76	73	80	75	72	79	75	72	78	74	72	70																																				
8	86	78	73	69	85	77	73	69	76	72	69	75	72	69	75	71	68	67																																				
9	83	75	70	66	82	74	69	66	73	69	66	72	69	66	72	68	65	64																																				
10	80	72	67	63	79	71	66	63	70	66	63	70	66	63	69	65	63	62																																				

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	485926
5°	468496
10°	412044
15°	322933
20°	223704
25°	137833
30°	76662
35°	40903
40°	20276
45°	10353
50°	5725
55°	3714
60°	1859
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P225451

CATALOG NUMBER: LD2B10D010 EU2B10FL409030D2W 2LBDLC*MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	109.9	19.7
10°-20°	220.0	39.4
20°-30°	150.3	26.9
30°-40°	57.3	10.2
40°-50°	15.9	2.8
50°-60°	5.0	0.9
60°-70°	0.5	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	480.2	85.9
0°-40°	537.4	96.2
0°-60°	558.3	99.9
0°-90°	558.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	558.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1254	
5°	1205	110
15°	805	220
25°	322	150
35°	86	57
45°	19	16
55°	6	5
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P225451

CATALOG NUMBER: LD2B10D010 EU2B10FL409030D2W 2LBDLC*MB

CANDELA DISTRIBUTION (FULL):

	0°
0°	1254.5
2.5°	1241.1
5°	1204.9
7.5°	1137.3
10°	1047.6
12.5°	933.6
15°	805.3
17.5°	674.0
20°	542.7
22.5°	426.3
25°	322.5
27.5°	236.7
30°	171.4
32.5°	121.9
35°	86.5
37.5°	60.5
40°	40.1
42.5°	26.7
45°	18.9
47.5°	13.4
50°	9.5
52.5°	7.1
55°	5.5
57.5°	3.9
60°	2.4
62.5°	0.8
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)