

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224286

Luminaire Tested: **LD2B20D010 EU2B20FL409727 2LBDSQLC\*MW**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P224286  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14835)  
Test Lab: INNOVATION CENTER (G1)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD2B20D010 EU2B20FL409727 2LBDSQLC\*MW  
Description: 2000 Lumen, 2inch Portfolio LED Downlight  
FLOOD OPTIC  
LENSED SQUARE CAST TRIM WITH MATTE WHITE FINISH  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1143.5 lumens  
Efficiency: N/A  
Efficacy: 54.7 lumens/watt  
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59  
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 20.9  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P224286

CATALOG NUMBER: LD2B20D010 EU2B20FL409727 2LBDSQLC\*MW

### Luminous Intensity Polar Plot





TEST NUMBER: P224286

CATALOG NUMBER: LD2B20D010 EU2B20FL409727 2LBDSQLC\*MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95			95
2	110	106	102	99	108	104	101	98	101	98	96	98	96	94	95	94	92	91			91
3	105	100	96	93	104	99	95	92	96	93	90	94	91	89	92	90	88	86			86
4	101	95	90	87	100	94	90	86	92	88	85	90	87	85	88	86	84	82			82
5	98	91	86	82	96	90	85	82	88	84	81	86	83	80	85	82	80	79			79
6	94	86	82	78	93	86	81	78	84	80	77	83	79	77	82	79	76	75			75
7	90	83	78	74	89	82	77	74	81	77	74	80	76	73	79	76	73	72			72
8	87	79	74	71	86	79	74	71	78	74	71	77	73	70	76	73	70	69			69
9	84	76	71	68	83	76	71	68	75	71	68	74	70	67	73	70	67	66			66
10	81	73	68	65	80	73	68	65	72	68	65	71	68	65	71	67	65	64			64

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1035221
5°	1016351
10°	903499
15°	710590
20°	472840
25°	271435
30°	137133
35°	64498
40°	25940
45°	12873
50°	7050
55°	4930
60°	4571
65°	2658
70°	3284
75°	2245
80°	3346
85°	0



TEST NUMBER: P224286

CATALOG NUMBER: LD2B20D010 EU2B20FL409727 2LBDSQLC\*MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	239.4	20.9
10°-20°	480.0	42.0
20°-30°	298.6	26.1
30°-40°	91.8	8.0
40°-50°	20.2	1.8
50°-60°	7.2	0.6
60°-70°	3.6	0.3
70°-80°	2.1	0.2
80°-90°	0.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1018.0	89.0
0°-40°	1109.8	97.1
0°-60°	1137.1	99.4
0°-90°	1143.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1143.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2673	
5°	2614	239
15°	1772	480
25°	635	299
35°	136	92
45°	24	20
55°	7	7
65°	3	4
75°	2	2
85°	0	1
90°	0	



TEST NUMBER: P224286

CATALOG NUMBER: LD2B20D010 EU2B20FL409727 2LBDSQLC\*MW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2672.6
2.5°	2660.9
5°	2613.9
7.5°	2495.1
10°	2297.1
12.5°	2059.5
15°	1772.0
17.5°	1458.1
20°	1147.1
22.5°	869.8
25°	635.1
27.5°	447.4
30°	306.6
32.5°	206.8
35°	136.4
37.5°	82.1
40°	51.3
42.5°	35.2
45°	23.5
47.5°	16.1
50°	11.7
52.5°	10.3
55°	7.3
57.5°	5.9
60°	5.9
62.5°	4.4
65°	2.9
67.5°	2.9
70°	2.9
72.5°	2.9
75°	1.5
77.5°	1.5
80°	1.5
82.5°	1.5
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)