

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P222358

Luminaire Tested: **LD2B20D010 EU2B20NFL259727 2LBDSQLC*MB**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P222358
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (155)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B20D010 EU2B20NFL259727 2LBDSQLC*MB
Description: 2000 Lumen, 2inch Portfolio LED Downlight
NARROW FLOOD OPTIC
LENSED SQUARE CAST TRIM WITH MATTE BLACK FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1124.1 lumens
Efficiency: N/A
Efficacy: 53.8 lumens/watt
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.35
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P222358

CATALOG NUMBER: LD2B20D010 EU2B20NFL259727 2LBDSQLC*MB

Luminous Intensity Polar Plot





TEST NUMBER: P222358

CATALOG NUMBER: LD2B20D010 EU2B20NFL259727 2LBDSQLC*MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	99	97
1	115	113	112	110	113	111	110	108	107	106	105	104	103	102	100	100	99	97	97	96	95
2	112	109	106	104	110	107	104	102	104	102	100	101	99	98	98	97	96	95	95	93	92
3	109	105	101	99	107	103	100	98	101	98	96	99	97	95	96	95	93	92	92	91	90
4	106	101	97	95	104	100	97	94	98	95	93	96	94	92	95	93	91	90	89	88	86
5	103	98	94	91	102	97	94	91	95	92	90	94	91	89	93	90	89	88	87	86	84
6	101	95	91	89	99	94	91	88	93	90	88	92	89	87	91	88	87	86	85	84	82
7	98	92	89	86	97	92	88	86	91	88	85	90	87	85	89	86	85	84	83	82	80
8	96	90	86	84	95	90	86	84	89	86	83	88	85	83	87	85	83	82	81	80	79
9	94	88	84	82	93	88	84	82	87	84	82	86	83	81	85	83	81	80	79	79	79
10	92	86	82	80	91	86	82	80	85	82	80	84	82	80	84	81	79	79	79	79	79

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2583172
5°	2385095
10°	1614388
15°	549223
20°	201733
25°	106933
30°	54969
35°	25676
40°	8394
45°	4273
50°	1989
55°	743
60°	852
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P222358

CATALOG NUMBER: LD2B20D010 EU2B20NFL259727 2LBDSQLC*MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	521.8	46.4
10°-20°	438.7	39.0
20°-30°	120.4	10.7
30°-40°	35.1	3.1
40°-50°	6.5	0.6
50°-60°	1.5	0.1
60°-70°	0.1	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1080.9	96.2
0°-40°	1116.0	99.3
0°-60°	1124.0	100.0
0°-90°	1124.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1124.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6669	
5°	6134	522
15°	1370	439
25°	250	120
35°	54	35
45°	8	6
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P222358

CATALOG NUMBER: LD2B20D010 EU2B20NFL259727 2LBDSQLC*MB

CANDELA DISTRIBUTION (FULL):

	0°
0°	6668.9
1°	6630.1
2°	6561.5
3°	6462.9
4°	6327.8
5°	6134.1
6°	5869.4
7°	5538.4
8°	5134.2
9°	4657.0
10°	4104.5
11°	3498.9
12°	2868.8
13°	2267.6
14°	1755.0
15°	1369.6
17.5°	772.8
20°	489.4
22.5°	348.8
25°	250.2
27.5°	177.2
30°	122.9
32.5°	86.4
35°	54.3
37.5°	22.1
40°	16.6
42.5°	12.2
45°	7.8
47.5°	4.4
50°	3.3
52.5°	2.2
55°	1.1
57.5°	1.1
60°	1.1
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P222358

CATALOG NUMBER: LD2B20D010 EU2B20NFL259727 2LBDSQLC*MB

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)