

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P264015

Luminaire Tested: **LD2B20D010 EU2B2010SP158030 2LBSQC\*MMS**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P264015  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1805-787-1)  
Test Lab: INNOVATION CENTER(G2)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD2B20D010 EU2B2010SP158030 2LBSQC\*MMS  
Description: 2000 Lumen, 2inch Portfolio LED Downlight  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1823.0 lumens  
Efficiency: N/A  
Efficacy: 87.2 lumens/watt  
Spacing Criteria (0/90/45): 0.28 / 0.28 / 0.28  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 20.9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P264015

CATALOG NUMBER: LD2B20D010 EU2B2010SP158030 2LBSQC\*MMS

### Luminous Intensity Polar Plot





TEST NUMBER: P264015

CATALOG NUMBER: LD2B20D010 EU2B2010SP158030 2LBSQC\*MMS

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						100													
1	116	114	112	111	113	112	110	109	108	107	106	104	103	102	101	100	100	98						98													
2	113	109	107	105	111	108	106	104	105	103	101	102	101	99	99	98	97	96						96													
3	110	106	103	100	108	105	102	100	102	100	98	100	98	97	98	96	95	94						94													
4	107	103	99	97	106	102	99	96	100	97	95	98	96	94	96	95	93	92						92													
5	105	100	97	94	104	99	96	94	98	95	93	96	94	92	95	93	91	90						90													
6	103	98	94	92	102	97	94	91	96	93	91	95	92	90	93	91	90	89						89													
7	101	95	92	90	100	95	92	89	94	91	89	93	90	89	92	90	88	87						87													
8	99	93	90	88	98	93	90	88	92	89	87	91	89	87	91	88	87	86						86													
9	97	92	88	86	96	91	88	86	91	88	86	90	87	86	89	87	85	85						85													
10	95	90	87	85	95	90	87	85	89	86	85	89	86	84	88	86	84	83						83													

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	8602009
5°	6894919
10°	3009343
15°	932607
20°	325095
25°	143603
30°	65001
35°	33788
40°	19257
45°	9140
50°	5757
55°	3183
60°	1875
65°	2218
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P264015

CATALOG NUMBER: LD2B20D010 EU2B2010SP158030 2LBSQC\*MMS

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	1057.2	58.0
10°-20°	579.0	31.8
20°-30°	132.0	7.2
30°-40°	37.9	2.1
40°-50°	11.7	0.6
50°-60°	3.5	0.2
60°-70°	1.6	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1768.2	97.0
0°-40°	1806.1	99.1
0°-60°	1821.4	99.9
0°-90°	1823.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1823.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	17436	
5°	13922	###
15°	1826	579
25°	264	132
35°	56	38
45°	13	12
55°	4	4
65°	2	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P264015

CATALOG NUMBER: LD2B20D010 EU2B2010SP158030 2LBSQC\*MMS

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	17435.5
1°	17218.5
2°	16767.7
3°	16068.0
4°	15106.4
5°	13922.2
6°	12470.5
7°	10848.6
8°	9155.5
9°	7516.7
10°	6007.0
11°	4729.3
12°	3722.8
13°	2929.6
14°	2314.1
15°	1825.9
16°	1440.5
17°	1146.8
18°	922.3
19°	750.2
20°	619.2
22.5°	400.3
25°	263.8
26°	222.6
27°	188.9
28°	159.0
29°	132.8
30°	114.1
32.5°	78.6
35°	56.1
37.5°	41.2
40°	29.9
42.5°	20.6
45°	13.1
47.5°	9.4
50°	7.5
52.5°	5.6
55°	3.7
57.5°	1.9
60°	1.9
62.5°	1.9
65°	1.9
67.5°	1.9



TEST NUMBER: P264015

CATALOG NUMBER: LD2B20D010 EU2B2010SP158030 2LBSQC\*MMS

**CANDELA DISTRIBUTION (continued):**

	0°
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







70°		0.0
72.5°		0.0



(END OF REPORT)