

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224953

Luminaire Tested: **LD2B20D010 EU2B20FL408030 2LBD*H**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P224953
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (156)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B20D010 EU2B20FL408030 2LBD*H
Description: 2000 Lumen, 2inch Portfolio LED Downlight
FLOOD OPTIC
SPUN ROUND TRIM WITH HAZE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1855.7 lumens
Efficiency: N/A
Efficacy: 88.8 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P224953

CATALOG NUMBER: LD2B20D010 EU2B20FL408030 2LBD*H

Luminous Intensity Polar Plot





TEST NUMBER: P224953

CATALOG NUMBER: LD2B20D010 EU2B20FL408030 2LBD*H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95			95
2	110	106	103	100	108	104	101	99	101	99	97	98	96	94	96	94	93	91			91
3	106	100	96	93	104	99	95	92	97	94	91	94	92	90	92	90	88	87			87
4	102	96	91	88	100	94	90	87	92	89	86	91	88	85	89	86	84	83			83
5	98	91	86	83	96	90	86	82	89	85	82	87	84	81	86	83	80	79			79
6	94	87	82	79	93	86	82	78	85	81	78	84	80	77	82	79	77	76			76
7	91	83	78	75	90	83	78	75	82	77	74	80	77	74	79	76	74	73			73
8	88	80	75	72	87	79	75	72	78	74	71	77	74	71	77	73	71	70			70
9	85	77	72	69	84	76	72	69	75	71	68	75	71	68	74	70	68	67			67
10	82	74	69	66	81	73	69	66	73	69	66	72	68	66	71	68	65	64			64

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1721249
5°	1685209
10°	1484159
15°	1164413
20°	773255
25°	443886
30°	222606
35°	102800
40°	41817
45°	18680
50°	9762
55°	6078
60°	2789
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P224953

CATALOG NUMBER: LD2B20D010 EU2B20FL408030 2LBD*H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	395.8	21.3
10°-20°	785.9	42.4
20°-30°	488.3	26.3
30°-40°	147.3	7.9
40°-50°	30.1	1.6
50°-60°	7.8	0.4
60°-70°	0.4	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1670.1	90.0
0°-40°	1817.4	97.9
0°-60°	1855.3	100.0
0°-90°	1855.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1855.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4444	
5°	4334	396
15°	2904	786
25°	1039	488
35°	217	147
45°	34	30
55°	9	8
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P224953

CATALOG NUMBER: LD2B20D010 EU2B20FL408030 2LBD*H

CANDELA DISTRIBUTION (FULL):

	0°
0°	4443.7
1°	4429.3
2°	4409.5
3°	4395.1
4°	4373.6
5°	4334.1
6°	4271.2
7°	4184.9
8°	4060.9
9°	3920.8
10°	3773.4
11°	3617.1
12°	3453.6
13°	3282.9
14°	3096.0
15°	2903.7
17.5°	2388.0
20°	1875.9
22.5°	1423.1
25°	1038.6
27.5°	733.1
30°	497.7
32.5°	327.0
35°	217.4
37.5°	134.8
40°	82.7
42.5°	53.9
45°	34.1
47.5°	21.6
50°	16.2
52.5°	10.8
55°	9.0
57.5°	5.4
60°	3.6
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P224953

CATALOG NUMBER: LD2B20D010 EU2B20FL408030 2LBD*H

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)