

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224316

Luminaire Tested: **LD2B15D010 EU2B15FL409024 2LBDSQLC*MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P224316
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14835)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B15D010 EU2B15FL409024 2LBDSQLC*MW
Description: 1500 Lumen, 2inch Portfolio LED Downlight
FLOOD OPTIC
LENSED SQUARE CAST TRIM WITH MATTE WHITE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 874.6 lumens
Efficiency: N/A
Efficacy: 61.2 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P224316

CATALOG NUMBER: LD2B15D010 EU2B15FL409024 2LBDSQLC*MW

Luminous Intensity Polar Plot



0% Up
100% Dn



TEST NUMBER: P224316

CATALOG NUMBER: LD2B15D010 EU2B15FL409024 2LBDSQLC*MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95			95
2	110	106	102	99	108	104	101	98	101	98	96	98	96	94	95	94	92	91			91
3	105	100	96	93	104	99	95	92	96	93	90	94	91	89	92	90	88	86			86
4	101	95	90	87	100	94	90	86	92	88	85	90	87	85	88	86	84	82			82
5	98	91	86	82	96	90	85	82	88	84	81	86	83	80	85	82	80	79			79
6	94	87	82	78	93	86	81	78	84	80	77	83	80	77	82	79	76	75			75
7	90	83	78	74	89	82	77	74	81	77	74	80	76	73	79	76	73	72			72
8	87	79	74	71	86	79	74	71	78	74	71	77	73	70	76	73	70	69			69
9	84	76	71	68	83	76	71	68	75	71	68	74	70	67	73	70	67	66			66
10	81	73	68	65	80	73	68	65	72	68	65	71	68	65	71	67	65	64			64

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	791774
5°	777379
10°	691026
15°	543489
20°	361627
25°	207626
30°	104884
35°	49320
40°	19872
45°	9860
50°	5423
55°	3782
60°	3486
65°	2016
70°	2492
75°	1646
80°	2454
85°	0



TEST NUMBER: P224316

CATALOG NUMBER: LD2B15D010 EU2B15FL409024 2LBDSQLC*MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	183.1	20.9
10°-20°	367.1	42.0
20°-30°	228.4	26.1
30°-40°	70.2	8.0
40°-50°	15.4	1.8
50°-60°	5.5	0.6
60°-70°	2.8	0.3
70°-80°	1.6	0.2
80°-90°	0.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	778.6	89.0
0°-40°	848.8	97.1
0°-60°	869.8	99.5
0°-90°	874.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	874.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2044	
5°	1999	183
15°	1355	367
25°	486	228
35°	104	70
45°	18	15
55°	6	6
65°	2	3
75°	1	2
85°	0	0
90°	0	



TEST NUMBER: P224316

CATALOG NUMBER: LD2B15D010 EU2B15FL409024 2LBDSQLC*MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	2044.1
2.5°	2035.2
5°	1999.3
7.5°	1908.4
10°	1756.9
12.5°	1575.2
15°	1355.3
17.5°	1115.2
20°	877.3
22.5°	665.3
25°	485.8
27.5°	342.2
30°	234.5
32.5°	158.2
35°	104.3
37.5°	62.8
40°	39.3
42.5°	26.9
45°	18.0
47.5°	12.3
50°	9.0
52.5°	7.9
55°	5.6
57.5°	4.5
60°	4.5
62.5°	3.4
65°	2.2
67.5°	2.2
70°	2.2
72.5°	2.2
75°	1.1
77.5°	1.1
80°	1.1
82.5°	1.1
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)