

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224323

Luminaire Tested: **LD2B20D010 EU2B20FL408030 2LBDSQLC*MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P224323
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14835)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B20D010 EU2B20FL408030 2LBDSQLC*MW
Description: 2000 Lumen, 2inch Portfolio LED Downlight
FLOOD OPTIC
LENSED SQUARE CAST TRIM WITH MATTE WHITE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1642.4 lumens
Efficiency: N/A
Efficacy: 78.6 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P224323

CATALOG NUMBER: LD2B20D010 EU2B20FL408030 2LBDSQLC*MW

Luminous Intensity Polar Plot





TEST NUMBER: P224323

CATALOG NUMBER: LD2B20D010 EU2B20FL408030 2LBDSQLC*MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95			
2	110	106	102	99	108	104	101	98	101	98	96	98	96	94	95	94	92	91			
3	105	100	96	93	104	99	95	92	96	93	90	94	91	89	92	90	88	86			
4	101	95	90	87	100	94	90	86	92	88	85	90	87	85	88	86	84	82			
5	98	91	86	82	96	90	85	82	88	84	81	86	83	80	85	82	80	79			
6	94	87	82	78	93	86	81	78	84	80	77	83	80	77	82	79	76	75			
7	90	83	78	74	89	82	77	74	81	77	74	80	76	73	79	76	73	72			
8	87	79	74	71	86	79	74	71	78	74	71	77	73	70	76	73	70	69			
9	84	76	71	68	83	76	71	68	75	71	68	74	70	67	73	70	67	66			
10	81	73	68	65	80	73	68	65	72	68	65	71	68	65	71	67	65	64			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1486983
5°	1459885
10°	1297764
15°	1020651
20°	679149
25°	389907
30°	196977
35°	92634
40°	37266
45°	18461
50°	10184
55°	7091
60°	6507
65°	3849
70°	4757
75°	3143
80°	4684
85°	0



TEST NUMBER: P224323

CATALOG NUMBER: LD2B20D010 EU2B20FL408030 2LBDSQLC*MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	343.9	20.9
10°-20°	689.4	42.0
20°-30°	428.9	26.1
30°-40°	131.9	8.0
40°-50°	29.0	1.8
50°-60°	10.3	0.6
60°-70°	5.2	0.3
70°-80°	3.0	0.2
80°-90°	0.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1462.2	89.0
0°-40°	1594.1	97.1
0°-60°	1633.4	99.4
0°-90°	1642.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1642.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3839	
5°	3755	344
15°	2545	689
25°	912	429
35°	196	132
45°	34	29
55°	10	10
65°	4	5
75°	2	3
85°	0	1
90°	0	



TEST NUMBER: P224323

CATALOG NUMBER: LD2B20D010 EU2B20FL408030 2LBDSQLC*MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	3838.9
2.5°	3822.0
5°	3754.6
7.5°	3583.9
10°	3299.5
12.5°	2958.2
15°	2545.2
17.5°	2094.3
20°	1647.6
22.5°	1249.4
25°	912.3
27.5°	642.6
30°	440.4
32.5°	297.1
35°	195.9
37.5°	118.0
40°	73.7
42.5°	50.6
45°	33.7
47.5°	23.2
50°	16.9
52.5°	14.7
55°	10.5
57.5°	8.4
60°	8.4
62.5°	6.3
65°	4.2
67.5°	4.2
70°	4.2
72.5°	4.2
75°	2.1
77.5°	2.1
80°	2.1
82.5°	2.1
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)