

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P263944

Luminaire Tested: **LD2B15D010 EU2B1510SP158027 2LBD*B**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P263944
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1805-787-1)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B15D010 EU2B1510SP158027 2LBD*B
Description: 1500 Lumen, 2inch Portfolio LED Downlight
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1273.0 lumens
Efficiency: N/A
Efficacy: 89.0 lumens/watt
Spacing Criteria (0/90/45): 0.28 / 0.28 / 0.28
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P263944

CATALOG NUMBER: LD2B15D010 EU2B1510SP158027 2LBD*B

Luminous Intensity Polar Plot





TEST NUMBER: P263944

CATALOG NUMBER: LD2B15D010 EU2B1510SP158027 2LBD*B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	116	114	112	111	113	112	110	109	108	107	106	104	103	102	101	100	100	98				98
2	113	109	107	105	111	108	106	104	105	103	101	102	101	99	99	98	97	96				96
3	110	106	103	100	108	105	102	100	102	100	98	100	98	97	98	96	95	94				94
4	107	103	99	97	106	102	99	96	100	97	95	98	96	94	96	95	93	92				92
5	105	100	97	94	104	99	96	94	98	95	93	96	94	92	95	93	91	90				90
6	103	98	94	92	102	97	94	91	96	93	91	95	92	90	93	91	90	89				89
7	101	95	92	90	100	95	92	89	94	91	89	93	90	89	92	90	88	87				87
8	99	93	90	88	98	93	90	88	92	89	87	91	89	87	91	88	87	86				86
9	97	92	88	86	96	91	88	86	91	88	86	90	87	86	89	87	85	85				85
10	95	90	87	85	95	90	87	85	89	86	85	89	86	84	88	86	84	83				83

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	6006778
5°	4814735
10°	2101430
15°	651226
20°	227021
25°	100272
30°	45404
35°	23610
40°	13460
45°	6349
50°	3991
55°	2236
60°	1283
65°	1518
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P263944

CATALOG NUMBER: LD2B15D010 EU2B1510SP158027 2LBD*B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	738.3	58.0
10°-20°	404.3	31.8
20°-30°	92.2	7.2
30°-40°	26.5	2.1
40°-50°	8.2	0.6
50°-60°	2.4	0.2
60°-70°	1.1	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1234.7	97.0
0°-40°	1261.2	99.1
0°-60°	1271.9	99.9
0°-90°	1273.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1273.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	12175	
5°	9722	738
15°	1275	404
25°	184	92
35°	39	26
45°	9	8
55°	3	2
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P263944

CATALOG NUMBER: LD2B15D010 EU2B1510SP158027 2LBD*B

CANDELA DISTRIBUTION (FULL):

	0°
0°	12175.2
1°	12023.7
2°	11708.9
3°	11220.3
4°	10548.8
5°	9721.9
6°	8708.2
7°	7575.5
8°	6393.3
9°	5248.9
10°	4194.7
11°	3302.5
12°	2599.6
13°	2045.8
14°	1616.0
15°	1275.0
16°	1005.9
17°	800.8
18°	644.0
19°	523.8
20°	432.4
22.5°	279.6
25°	184.2
26°	155.5
27°	131.9
28°	111.0
29°	92.8
30°	79.7
32.5°	54.9
35°	39.2
37.5°	28.7
40°	20.9
42.5°	14.4
45°	9.1
47.5°	6.5
50°	5.2
52.5°	3.9
55°	2.6
57.5°	1.3
60°	1.3
62.5°	1.3
65°	1.3
67.5°	1.3



TEST NUMBER: P263944

CATALOG NUMBER: LD2B15D010 EU2B1510SP158027 2LBD*B

CANDELA DISTRIBUTION (continued):

	0°
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







70°		0.0
72.5°		0.0



(END OF REPORT)