

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P225515

Luminaire Tested: **LD2B15D010 EU2B15FL408027 2LBDL\*H**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P225515  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14832)  
Test Lab: INNOVATION CENTER (G1)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD2B15D010 EU2B15FL408027 2LBDL\*H  
Description: 1500 Lumen, 2inch Portfolio LED Downlight  
FLOOD OPTIC  
LENSED SPUN ROUND TRIM WITH HAZE FINISH  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1266.1 lumens  
Efficiency: N/A  
Efficacy: 88.5 lumens/watt  
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.6  
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 14.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P225515

CATALOG NUMBER: LD2B15D010 EU2B15FL408027 2LBDL\*H

### Luminous Intensity Polar Plot





TEST NUMBER: P225515

CATALOG NUMBER: LD2B15D010 EU2B15FL408027 2LBDL\*H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	95	95	95
2	110	105	102	99	108	104	101	98	101	98	96	98	96	94	95	93	92	90	90	90	90
3	105	100	96	92	103	98	95	91	96	93	90	94	91	89	91	89	87	86	86	86	86
4	101	95	90	86	99	94	89	86	91	88	85	90	86	84	88	85	83	82	82	82	82
5	97	90	85	81	96	89	84	81	87	83	80	86	82	80	84	81	79	78	78	78	78
6	93	86	81	77	92	85	80	77	84	79	76	82	79	76	81	78	75	74	74	74	74
7	90	82	77	73	88	81	76	73	80	76	73	79	75	72	78	75	72	71	71	71	71
8	86	78	73	70	85	78	73	70	77	72	69	76	72	69	75	71	69	68	68	68	68
9	83	75	70	67	82	75	70	67	74	69	66	73	69	66	72	69	66	65	65	65	65
10	80	72	67	64	79	72	67	64	71	67	64	70	66	64	70	66	63	62	62	62	62

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1112961
5°	1075919
10°	949321
15°	747884
20°	513937
25°	310370
30°	168218
35°	86439
40°	42272
45°	20049
50°	10485
55°	7023
60°	4028
65°	1558
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P225515

CATALOG NUMBER: LD2B15D010 EU2B15FL408027 2LBDL\*H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	252.8	20.0
10°-20°	507.7	40.1
20°-30°	339.2	26.8
30°-40°	122.8	9.7
40°-50°	31.7	2.5
50°-60°	9.4	0.7
60°-70°	2.3	0.2
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1099.7	86.9
0°-40°	1222.6	96.6
0°-60°	1263.7	99.8
0°-90°	1266.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1266.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2873	
5°	2767	253
15°	1865	508
25°	726	339
35°	183	123
45°	37	32
55°	10	9
65°	2	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P225515

CATALOG NUMBER: LD2B15D010 EU2B15FL408027 2LBDL\*H

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2873.3
2.5°	2847.2
5°	2767.1
7.5°	2620.8
10°	2413.6
12.5°	2159.3
15°	1865.0
17.5°	1551.6
20°	1246.8
22.5°	966.5
25°	726.2
27.5°	529.4
30°	376.1
32.5°	264.7
35°	182.8
37.5°	127.1
40°	83.6
42.5°	54.0
45°	36.6
47.5°	26.1
50°	17.4
52.5°	13.9
55°	10.4
57.5°	7.0
60°	5.2
62.5°	3.5
65°	1.7
67.5°	1.7
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)