

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224798

Luminaire Tested: **LD2B15D010 EU2B15FL408027 2LBDL**MW***

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P224798
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14835)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B15D010 EU2B15FL408027 2LBDL*MW
Description: 1500 Lumen, 2inch Portfolio LED Downlight
FLOOD OPTIC
LENSED SPUN ROUND TRIM WITH MATTE WHITE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1266.0 lumens
Efficiency: N/A
Efficacy: 88.5 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P224798

CATALOG NUMBER: LD2B15D010 EU2B15FL408027 2LBDL*MW

Luminous Intensity Polar Plot





TEST NUMBER: P224798

CATALOG NUMBER: LD2B15D010 EU2B15FL408027 2LBDL*MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95			95																
2	110	106	102	99	108	104	101	98	101	98	96	98	96	94	95	94	92	91			91																
3	105	100	96	93	104	99	95	92	96	93	90	94	91	89	92	90	88	86			86																
4	101	95	90	87	100	94	90	86	92	88	85	90	87	85	88	86	84	82			82																
5	98	91	86	82	96	90	85	82	88	84	81	86	83	80	85	82	80	79			79																
6	94	87	82	78	93	86	81	78	84	80	77	83	80	77	82	79	76	75			75																
7	90	83	78	74	89	82	77	74	81	77	74	80	76	73	79	76	73	72			72																
8	87	79	74	71	86	79	74	71	78	74	71	77	73	70	76	73	70	69			69																
9	84	76	71	68	83	76	71	68	75	71	68	74	70	67	73	70	67	66			66																
10	81	73	68	65	80	73	68	65	72	68	65	71	68	65	71	67	65	64			64																

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1146196
5°	1125339
10°	1000374
15°	786742
20°	523542
25°	300540
30°	151803
35°	71402
40°	28721
45°	14243
50°	7834
55°	5470
60°	5035
65°	2933
70°	3624
75°	2395
80°	3569
85°	0



TEST NUMBER: P224798

CATALOG NUMBER: LD2B15D010 EU2B15FL408027 2LBDL*MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	265.1	20.9
10°-20°	531.5	42.0
20°-30°	330.6	26.1
30°-40°	101.6	8.0
40°-50°	22.3	1.8
50°-60°	8.0	0.6
60°-70°	4.0	0.3
70°-80°	2.3	0.2
80°-90°	0.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1127.1	89.0
0°-40°	1228.8	97.1
0°-60°	1259.1	99.5
0°-90°	1266.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1266.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2959	
5°	2894	265
15°	1962	531
25°	703	331
35°	151	102
45°	26	22
55°	8	8
65°	3	4
75°	2	2
85°	0	1
90°	0	



TEST NUMBER: P224798

CATALOG NUMBER: LD2B15D010 EU2B15FL408027 2LBDL*MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	2959.1
2.5°	2946.2
5°	2894.2
7.5°	2762.6
10°	2543.4
12.5°	2280.3
15°	1961.9
17.5°	1614.4
20°	1270.1
22.5°	963.1
25°	703.2
27.5°	495.4
30°	339.4
32.5°	229.0
35°	151.0
37.5°	91.0
40°	56.8
42.5°	39.0
45°	26.0
47.5°	17.9
50°	13.0
52.5°	11.4
55°	8.1
57.5°	6.5
60°	6.5
62.5°	4.9
65°	3.2
67.5°	3.2
70°	3.2
72.5°	3.2
75°	1.6
77.5°	1.6
80°	1.6
82.5°	1.6
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)