

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224375

Luminaire Tested: **LD2B15D010 EU2B15FL408027 2LBDSQC*MMS**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P224375
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14831)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B15D010 EU2B15FL408027 2LBDSQC*MMS
Description: 1500 Lumen, 2inch Portfolio LED Downlight
FLOOD OPTIC
SQUARE CAST TRIM WITH MATTE METALLIC SILVER
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1288.0 lumens
Efficiency: N/A
Efficacy: 90.1 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P224375

CATALOG NUMBER: LD2B15D010 EU2B15FL408027 2LBDSQC*MMS

Luminous Intensity Polar Plot





TEST NUMBER: P224375

CATALOG NUMBER: LD2B15D010 EU2B15FL408027 2LBDSQC*MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95			
2	110	106	102	100	108	104	101	99	101	99	96	98	96	94	95	94	92	91			
3	106	100	96	93	104	99	95	92	97	93	91	94	92	89	92	90	88	87			
4	102	95	91	87	100	94	90	87	92	89	86	90	87	85	89	86	84	83			
5	98	91	86	83	96	90	86	82	88	85	82	87	83	81	85	82	80	79			
6	94	87	82	78	93	86	82	78	85	81	78	83	80	77	82	79	77	76			
7	91	83	78	75	89	82	78	75	81	77	74	80	77	74	79	76	73	72			
8	87	80	75	71	86	79	75	71	78	74	71	77	73	71	76	73	70	69			
9	84	76	72	68	83	76	71	68	75	71	68	74	71	68	74	70	68	67			
10	81	74	69	66	81	73	69	66	72	68	65	72	68	65	71	68	65	64			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1172380
5°	1149874
10°	1021416
15°	806070
20°	537598
25°	309430
30°	156723
35°	73483
40°	30086
45°	13585
50°	6990
55°	4457
60°	2556
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P224375

CATALOG NUMBER: LD2B15D010 EU2B15FL408027 2LBDSQC*MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	270.7	21.0
10°-20°	543.2	42.2
20°-30°	340.2	26.4
30°-40°	105.3	8.2
40°-50°	21.7	1.7
50°-60°	6.1	0.5
60°-70°	0.8	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1154.0	89.6
0°-40°	1259.3	97.8
0°-60°	1287.1	99.9
0°-90°	1288.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1288.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3027	
5°	2957	271
15°	2010	543
25°	724	340
35°	155	105
45°	25	22
55°	7	6
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P224375

CATALOG NUMBER: LD2B15D010 EU2B15FL408027 2LBDSQC*MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	3026.7
2.5°	3011.8
5°	2957.3
7.5°	2818.4
10°	2596.9
12.5°	2324.2
15°	2010.1
17.5°	1648.1
20°	1304.2
22.5°	991.8
25°	724.0
27.5°	509.1
30°	350.4
32.5°	234.7
35°	155.4
37.5°	97.5
40°	59.5
42.5°	38.0
45°	24.8
47.5°	16.5
50°	11.6
52.5°	8.3
55°	6.6
57.5°	5.0
60°	3.3
62.5°	1.7
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)