

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P#

Luminaire Tested: **LD2B15D010 EU2B1510NFL259040 2LBPIN**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P#  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14816)  
Test Lab: INNOVATION CENTER (G1)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD2B15D010 EU2B1510NFL259040 2LBPIN  
Description: 1500 Lumen, 2inch Portfolio LED Downlight  
NARROW FLOOD OPTIC  
ROUND PINHOLE BLACK OCULUS  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 925.3 lumens  
Efficiency: N/A  
Efficacy: 64.7 lumens/watt  
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.35  
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 14.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P#

CATALOG NUMBER: LD2B15D010 EU2B1510NFL259040 2LBPIN

### Luminous Intensity Polar Plot





TEST NUMBER: P#

CATALOG NUMBER: LD2B15D010 EU2B1510NFL259040 2LBPIN

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	115	113	112	110	113	111	110	108	107	106	105	104	103	102	100	100	99	97	97	97	97
2	112	109	106	104	110	107	105	103	104	102	100	101	100	98	99	97	96	95	95	95	95
3	109	105	102	99	107	104	101	98	101	99	97	99	97	95	97	95	94	93	93	93	93
4	106	101	98	95	105	100	97	95	98	96	94	97	94	93	95	93	92	90	90	90	90
5	104	98	95	92	102	98	94	92	96	93	91	95	92	90	93	91	89	88	88	88	88
6	101	96	92	89	100	95	91	89	94	91	88	92	90	88	91	89	87	86	86	86	86
7	99	93	89	87	98	93	89	87	92	88	86	91	88	86	90	87	85	85	85	85	85
8	97	91	87	85	96	90	87	85	90	86	84	89	86	84	88	86	84	83	83	83	83
9	95	89	85	83	94	88	85	83	88	85	82	87	84	82	86	84	82	81	81	81	81
10	93	87	83	81	92	87	83	81	86	83	81	85	83	81	85	82	80	80	80	80	80

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	2172708
5°	2017642
10°	1371337
15°	453666
20°	154096
25°	78069
30°	40313
35°	13245
40°	4907
45°	2685
50°	723
55°	811
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P#

CATALOG NUMBER: LD2B15D010 EU2B1510NFL259040 2LBPIN

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	440.6	47.6
10°-20°	368.1	39.8
20°-30°	89.0	9.6
30°-40°	23.0	2.5
40°-50°	3.8	0.4
50°-60°	0.7	0.1
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	897.8	97.0
0°-40°	920.8	99.5
0°-60°	925.3	100.0
0°-90°	925.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	925.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	5607	
5°	5187	441
15°	1131	368
25°	183	89
35°	28	23
45°	5	4
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P#

CATALOG NUMBER: LD2B15D010 EU2B1510NFL259040 2LBPIN

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	5607.2
2.5°	5513.4
5°	5187.2
7.5°	4511.6
10°	3485.3
12.5°	2156.0
15°	1130.9
17.5°	611.1
20°	373.7
22.5°	258.1
25°	182.6
27.5°	129.0
30°	90.1
32.5°	63.3
35°	28.0
37.5°	12.2
40°	9.7
42.5°	7.3
45°	4.9
47.5°	2.4
50°	1.2
52.5°	1.2
55°	1.2
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)