

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P264927

Luminaire Tested: **LD2B15D010 EU2B1510SP159027 2LBDL\*H**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P264927  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1711-432-2)  
Test Lab: INNOVATION CENTER(G3)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD2B15D010 EU2B1510SP159027 2LBDL\*H  
Description: 1500 Lumen, 2inch Portfolio LED Downlight  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 957.0 lumens  
Efficiency: N/A  
Efficacy: 66.9 lumens/watt  
Spacing Criteria (0/90/45): 0.31 / 0.31 / 0.32  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 14.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P264927

CATALOG NUMBER: LD2B15D010 EU2B1510SP159027 2LBDL\*H

### Luminous Intensity Polar Plot





TEST NUMBER: P264927

CATALOG NUMBER: LD2B15D010 EU2B1510SP159027 2LBDL\*H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	113	111	110	113	111	110	108	107	106	105	104	103	102	100	99	99	97
2	112	108	106	103	110	107	104	102	104	102	100	101	99	98	98	97	96	94
3	109	104	101	98	107	103	100	97	100	98	96	98	96	94	96	94	93	92
4	106	100	97	94	104	99	96	93	97	95	92	96	93	91	94	92	90	89
5	103	97	93	91	101	96	93	90	95	92	89	93	91	89	92	90	88	87
6	100	94	90	88	99	94	90	87	92	89	87	91	88	86	90	88	86	85
7	98	92	88	85	97	91	88	85	90	87	85	89	86	84	88	86	84	83
8	95	89	86	83	94	89	85	83	88	85	82	87	84	82	86	84	82	81
9	93	87	83	81	92	87	83	81	86	83	81	85	82	80	85	82	80	79
10	91	85	82	79	91	85	81	79	84	81	79	84	81	79	83	80	79	78

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	3378394
5°	2749707
10°	1485334
15°	592233
20°	237469
25°	113718
30°	58962
35°	31138
40°	17260
45°	10675
50°	7368
55°	4903
60°	3750
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P264927

CATALOG NUMBER: LD2B15D010 EU2B1510SP159027 2LBDL\*H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	446.5	46.7
10°-20°	352.3	36.8
20°-30°	103.9	10.9
30°-40°	34.6	3.6
40°-50°	13.0	1.4
50°-60°	5.7	0.6
60°-70°	0.9	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	902.7	94.3
0°-40°	937.3	97.9
0°-60°	956.0	99.9
0°-90°	957.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	957.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	6848	
5°	5552	447
15°	1160	352
25°	209	104
35°	52	35
45°	15	13
55°	6	6
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P264927

CATALOG NUMBER: LD2B15D010 EU2B1510SP159027 2LBDL\*H

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	6847.7
2.5°	6571.7
5°	5552.2
7.5°	4277.7
10°	2964.9
12.5°	1897.4
15°	1159.5
17.5°	707.2
20°	452.3
22.5°	302.8
25°	208.9
27.5°	147.6
30°	103.5
32.5°	72.8
35°	51.7
37.5°	36.4
40°	26.8
42.5°	21.1
45°	15.3
47.5°	13.4
50°	9.6
52.5°	7.7
55°	5.7
57.5°	5.7
60°	3.8
62.5°	1.9
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)