

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P264938

Luminaire Tested: **LD2B15D010 EU2B1510SP159027 2LBSQLC\*MMS**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P264938  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1711-432-2)  
Test Lab: INNOVATION CENTER(G3)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD2B15D010 EU2B1510SP159027 2LBSQLC\*MMS  
Description: 1500 Lumen, 2inch Portfolio LED Downlight  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 902.0 lumens  
Efficiency: N/A  
Efficacy: 63.1 lumens/watt  
Spacing Criteria (0/90/45): 0.31 / 0.31 / 0.32  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 14.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P264938

CATALOG NUMBER: LD2B15D010 EU2B1510SP159027 2LBSQLC\*MMS

### Luminous Intensity Polar Plot





TEST NUMBER: P264938

CATALOG NUMBER: LD2B15D010 EU2B1510SP159027 2LBSQLC\*MMS

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	113	111	110	113	111	110	108	107	106	105	104	103	102	100	99	99	97
2	112	108	106	103	110	107	104	102	104	102	100	101	99	98	98	97	96	94
3	109	104	101	98	107	103	100	97	100	98	96	98	96	94	96	94	93	92
4	106	100	97	94	104	99	96	93	97	95	92	96	93	91	94	92	90	89
5	103	97	93	91	101	96	93	90	95	92	89	93	91	89	92	90	88	87
6	100	94	90	88	99	94	90	87	92	89	87	91	88	86	90	88	86	85
7	98	92	88	85	97	91	88	85	90	87	85	89	86	84	88	86	84	83
8	95	89	86	83	94	89	85	83	88	85	82	87	84	82	86	84	82	81
9	93	87	83	81	92	87	83	81	86	83	81	85	82	80	85	82	80	79
10	91	85	82	79	91	85	81	79	84	81	79	84	81	79	83	80	78	78

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	3184256
5°	2591674
10°	1399968
15°	558216
20°	223818
25°	107185
30°	55544
35°	29391
40°	16294
45°	10117
50°	6908
55°	4645
60°	3552
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P264938

CATALOG NUMBER: LD2B15D010 EU2B1510SP159027 2LBSQLC\*MMS

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	420.8	46.7
10°-20°	332.1	36.8
20°-30°	97.9	10.9
30°-40°	32.6	3.6
40°-50°	12.3	1.4
50°-60°	5.4	0.6
60°-70°	0.9	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	850.8	94.3
0°-40°	883.4	97.9
0°-60°	901.1	99.9
0°-90°	902.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	902.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	6454	
5°	5233	421
15°	1093	332
25°	197	98
35°	49	33
45°	14	12
55°	5	5
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P264938

CATALOG NUMBER: LD2B15D010 EU2B1510SP159027 2LBSQLC\*MMS

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	6454.2
2.5°	6194.1
5°	5233.1
7.5°	4031.8
10°	2794.5
12.5°	1788.3
15°	1092.9
17.5°	666.6
20°	426.3
22.5°	285.4
25°	196.9
27.5°	139.1
30°	97.5
32.5°	68.6
35°	48.8
37.5°	34.3
40°	25.3
42.5°	19.9
45°	14.5
47.5°	12.6
50°	9.0
52.5°	7.2
55°	5.4
57.5°	5.4
60°	3.6
62.5°	1.8
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)