

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P222213

Luminaire Tested: **LD2B20D010 EU2B20NFL259730 2LBDSQC*MMS**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P222213
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (155)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B20D010 EU2B20NFL259730 2LBDSQC*MMS
Description: 2000 Lumen, 2inch Portfolio LED Downlight
NARROW FLOOD OPTIC
SQUARE CAST TRIM WITH MATTE METALLIC SILVER
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1303.4 lumens
Efficiency: N/A
Efficacy: 62.4 lumens/watt
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.35
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P222213

CATALOG NUMBER: LD2B20D010 EU2B20NFL259730 2LBDSQC*MMS

Luminous Intensity Polar Plot





TEST NUMBER: P222213

CATALOG NUMBER: LD2B20D010 EU2B20NFL259730 2LBDSQC*MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	113	112	110	113	111	110	108	107	106	105	104	103	102	100	100	99	97
2	112	109	106	104	110	107	104	102	104	102	100	101	99	98	98	97	96	95
3	109	105	101	99	107	103	100	98	101	98	96	99	97	95	96	95	93	92
4	106	101	97	95	104	100	97	94	98	95	93	96	94	92	95	93	91	90
5	103	98	94	91	102	97	94	91	95	92	90	94	91	89	93	90	89	88
6	101	95	91	89	99	94	91	88	93	90	88	92	89	87	91	88	87	86
7	98	92	89	86	97	92	88	86	91	88	85	90	87	85	89	86	85	84
8	96	90	86	84	95	90	86	84	89	86	83	88	85	83	87	85	83	82
9	94	88	84	82	93	88	84	82	87	84	82	86	83	81	85	83	81	80
10	92	86	82	80	91	86	82	80	85	82	80	84	82	80	84	81	79	79

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2995192
5°	2765522
10°	1871895
15°	636844
20°	233926
25°	123986
30°	63736
35°	29743
40°	9759
45°	4930
50°	2350
55°	878
60°	1007
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P222213

CATALOG NUMBER: LD2B20D010 EU2B20NFL259730 2LBDSQC*MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	605.0	46.4
10°-20°	508.7	39.0
20°-30°	139.6	10.7
30°-40°	40.7	3.1
40°-50°	7.5	0.6
50°-60°	1.7	0.1
60°-70°	0.2	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1253.3	96.2
0°-40°	1294.0	99.3
0°-60°	1303.3	100.0
0°-90°	1303.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1303.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7733	
5°	7112	605
15°	1588	509
25°	290	140
35°	63	41
45°	9	8
55°	1	2
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P222213

CATALOG NUMBER: LD2B20D010 EU2B20NFL259730 2LBDSQC*MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	7732.6
1°	7687.6
2°	7608.0
3°	7493.8
4°	7337.2
5°	7112.5
6°	6805.6
7°	6421.8
8°	5953.2
9°	5399.8
10°	4759.2
11°	4056.9
12°	3326.4
13°	2629.3
14°	2034.9
15°	1588.1
17.5°	896.1
20°	567.5
22.5°	404.4
25°	290.1
27.5°	205.4
30°	142.5
32.5°	100.1
35°	62.9
37.5°	25.7
40°	19.3
42.5°	14.1
45°	9.0
47.5°	5.1
50°	3.9
52.5°	2.6
55°	1.3
57.5°	1.3
60°	1.3
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P222213

CATALOG NUMBER: LD2B20D010 EU2B20NFL259730 2LBDSQC*MMS

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)