

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P264792

Luminaire Tested: **LD2B20D010 EU2B2010SP158040 2LBLC*MMS**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P264792
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1711-432-2)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B20D010 EU2B2010SP158040 2LBLC*MMS
Description: 2000 Lumen, 2inch Portfolio LED Downlight
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1771.0 lumens
Efficiency: N/A
Efficacy: 84.7 lumens/watt
Spacing Criteria (0/90/45): 0.31 / 0.31 / 0.32
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P264792

CATALOG NUMBER: LD2B20D010 EU2B2010SP158040 2LBLC*MMS

Luminous Intensity Polar Plot





TEST NUMBER: P264792

CATALOG NUMBER: LD2B20D010 EU2B2010SP158040 2LBLC*MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						100													
1	115	113	111	110	113	111	110	108	107	106	105	104	103	102	100	99	99	97						97													
2	112	108	106	103	110	107	104	102	104	102	100	101	99	98	98	97	96	94						94													
3	109	104	101	98	107	103	100	97	100	98	96	98	96	94	96	94	93	92						92													
4	106	100	97	94	104	99	96	93	97	95	92	96	93	91	94	92	90	89						89													
5	103	97	93	91	101	96	93	90	95	92	89	93	91	89	92	90	88	87						87													
6	100	94	90	88	99	94	90	87	92	89	87	91	88	86	90	88	86	85						85													
7	98	92	88	85	97	91	88	85	90	87	85	89	86	84	88	86	84	83						83													
8	95	89	86	83	94	89	85	83	88	85	82	87	84	82	86	84	82	81						81													
9	93	87	83	81	92	87	83	81	86	83	81	85	82	80	85	82	80	79						79													
10	91	85	82	79	91	85	81	79	84	81	79	84	81	79	83	80	78	78						78													

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	6251979
5°	5088508
10°	2748687
15°	1095950
20°	439446
25°	210451
30°	109095
35°	57699
40°	32009
45°	19815
50°	13585
55°	9118
60°	7006
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P264792

CATALOG NUMBER: LD2B20D010 EU2B2010SP158040 2LBLC*MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	826.3	46.7
10°-20°	651.9	36.8
20°-30°	192.3	10.9
30°-40°	64.0	3.6
40°-50°	24.1	1.4
50°-60°	10.6	0.6
60°-70°	1.7	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1670.6	94.3
0°-40°	1734.6	97.9
0°-60°	1769.3	99.9
0°-90°	1771.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1771.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	12672	
5°	10275	826
15°	2146	652
25°	387	192
35°	96	64
45°	28	24
55°	11	11
65°	0	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P264792

CATALOG NUMBER: LD2B20D010 EU2B2010SP158040 2LBLC*MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	12672.2
2.5°	12161.5
5°	10274.7
7.5°	7916.2
10°	5486.7
12.5°	3511.2
15°	2145.7
17.5°	1308.7
20°	837.0
22.5°	560.4
25°	386.6
27.5°	273.1
30°	191.5
32.5°	134.8
35°	95.8
37.5°	67.4
40°	49.7
42.5°	39.0
45°	28.4
47.5°	24.8
50°	17.7
52.5°	14.2
55°	10.6
57.5°	10.6
60°	7.1
62.5°	3.5
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)