

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P#

Luminaire Tested: **LD2B15D010 EU2B1510NFL259727 2LBPIN**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P#
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14816)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B15D010 EU2B1510NFL259727 2LBPIN
Description: 1500 Lumen, 2inch Portfolio LED Downlight
NARROW FLOOD OPTIC
ROUND PINHOLE BLACK OCULUS
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 752.4 lumens
Efficiency: N/A
Efficacy: 52.6 lumens/watt
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.35
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P#

CATALOG NUMBER: LD2B15D010 EU2B1510NFL259727 2LBPIN

Luminous Intensity Polar Plot





TEST NUMBER: P#

CATALOG NUMBER: LD2B15D010 EU2B1510NFL259727 2LBPIN

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	115	113	112	110	113	111	110	108	107	106	105	104	103	102	100	100	99	97	97	97	97
2	112	109	106	104	110	107	105	103	104	102	100	101	100	98	99	97	96	95	95	95	95
3	109	105	102	99	107	104	101	98	101	99	97	99	97	95	97	95	94	93	93	93	93
4	106	101	98	95	105	100	97	95	98	96	94	97	94	93	95	93	92	90	90	90	90
5	104	98	95	92	102	98	94	92	96	93	91	95	92	90	93	91	89	88	88	88	88
6	101	96	92	89	100	95	91	89	94	91	88	92	90	88	91	89	87	86	86	86	86
7	99	93	89	87	98	93	89	87	92	88	86	91	88	86	90	87	85	85	85	85	85
8	97	91	87	85	96	90	87	85	90	86	84	89	86	84	88	85	84	83	83	83	83
9	95	89	85	83	94	88	85	83	88	85	82	87	84	82	86	84	82	81	81	81	81
10	93	87	83	81	92	87	83	81	86	83	81	85	83	81	85	82	80	80	80	80	80

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1766701
5°	1640618
10°	1115114
15°	368902
20°	125314
25°	63490
30°	32797
35°	10785
40°	3996
45°	2192
50°	603
55°	676
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P#

CATALOG NUMBER: LD2B15D010 EU2B1510NFL259727 2LBPIN

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	358.3	47.6
10°-20°	299.3	39.8
20°-30°	72.4	9.6
30°-40°	18.7	2.5
40°-50°	3.1	0.4
50°-60°	0.5	0.1
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	730.1	97.0
0°-40°	748.8	99.5
0°-60°	752.4	100.0
0°-90°	752.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	752.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4559	
5°	4218	358
15°	920	299
25°	148	72
35°	23	19
45°	4	3
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P#

CATALOG NUMBER: LD2B15D010 EU2B1510NFL259727 2LBPIN

CANDELA DISTRIBUTION (FULL):

	0°
0°	4559.4
2.5°	4483.2
5°	4217.9
7.5°	3668.5
10°	2834.1
12.5°	1753.1
15°	919.6
17.5°	496.9
20°	303.9
22.5°	209.9
25°	148.5
27.5°	104.9
30°	73.3
32.5°	51.5
35°	22.8
37.5°	9.9
40°	7.9
42.5°	5.9
45°	4.0
47.5°	2.0
50°	1.0
52.5°	1.0
55°	1.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)