

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P223185

Luminaire Tested: **LD2B20D010 EU2B20NFL258040 2LBDSQC*MMS**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P223185
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (155)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B20D010 EU2B20NFL258040 2LBDSQC*MMS
Description: 2000 Lumen, 2inch Portfolio LED Downlight
NARROW FLOOD OPTIC
SQUARE CAST TRIM WITH MATTE METALLIC SILVER
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1853.3 lumens
Efficiency: N/A
Efficacy: 88.7 lumens/watt
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.35
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P223185

CATALOG NUMBER: LD2B20D010 EU2B20NFL258040 2LBDSQC*MMS

Luminous Intensity Polar Plot





TEST NUMBER: P223185

CATALOG NUMBER: LD2B20D010 EU2B20NFL258040 2LBDSQC*MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						100													
1	115	113	112	110	113	111	110	108	107	106	105	104	103	102	100	100	99	97						97													
2	112	109	106	104	110	107	104	102	104	102	100	101	99	98	98	97	96	95						95													
3	109	105	101	99	107	103	100	98	101	98	96	99	97	95	96	95	93	92						92													
4	106	101	97	95	104	100	97	94	98	95	93	96	94	92	95	93	91	90						90													
5	103	98	94	91	102	97	94	91	95	92	90	94	91	89	93	90	89	88						88													
6	101	95	91	89	99	94	91	88	93	90	88	92	89	87	91	88	87	86						86													
7	98	92	89	86	97	92	88	86	91	88	85	90	87	85	89	86	85	84						84													
8	96	90	86	84	95	90	86	84	89	86	83	88	85	83	87	85	83	82						82													
9	94	88	84	82	93	88	84	82	87	84	82	86	83	81	85	83	81	80						80													
10	92	86	82	80	91	86	82	80	85	82	80	84	82	80	84	81	79	79						79													

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	4258830
5°	3932271
10°	2661645
15°	905521
20°	332608
25°	176341
30°	90617
35°	42274
40°	13855
45°	7012
50°	3314
55°	1216
60°	1394
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P223185

CATALOG NUMBER: LD2B20D010 EU2B20NFL258040 2LBDSQC*MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	860.3	46.4
10°-20°	723.3	39.0
20°-30°	198.5	10.7
30°-40°	57.9	3.1
40°-50°	10.7	0.6
50°-60°	2.4	0.1
60°-70°	0.2	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1782.1	96.2
0°-40°	1839.9	99.3
0°-60°	1853.1	100.0
0°-90°	1853.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1853.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	10995	
5°	10113	860
15°	2258	723
25°	413	199
35°	89	58
45°	13	11
55°	2	2
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P223185

CATALOG NUMBER: LD2B20D010 EU2B20NFL258040 2LBDSQC*MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	10994.9
1°	10931.0
2°	10817.9
3°	10655.4
4°	10432.7
5°	10113.2
6°	9676.9
7°	9131.1
8°	8464.8
9°	7678.0
10°	6767.1
11°	5768.6
12°	4729.8
13°	3738.6
14°	2893.4
15°	2258.1
17.5°	1274.2
20°	806.9
22.5°	575.0
25°	412.6
27.5°	292.1
30°	202.6
32.5°	142.4
35°	89.4
37.5°	36.5
40°	27.4
42.5°	20.1
45°	12.8
47.5°	7.3
50°	5.5
52.5°	3.7
55°	1.8
57.5°	1.8
60°	1.8
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P223185

CATALOG NUMBER: LD2B20D010 EU2B20NFL258040 2LBDSQC*MMS

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)