

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P223187

Luminaire Tested: **LD2B20D010 EU2B20NFL258040 2LBDSQLC\*MB**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P223187  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (155)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD2B20D010 EU2B20NFL258040 2LBDSQLC\*MB  
Description: 2000 Lumen, 2inch Portfolio LED Downlight  
NARROW FLOOD OPTIC  
LENSED SQUARE CAST TRIM WITH MATTE BLACK FINISH  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1703.1 lumens  
Efficiency: N/A  
Efficacy: 81.5 lumens/watt  
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.35  
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 20.9  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P223187

CATALOG NUMBER: LD2B20D010 EU2B20NFL258040 2LBDSQLC\*MB

### Luminous Intensity Polar Plot





TEST NUMBER: P223187

CATALOG NUMBER: LD2B20D010 EU2B20NFL258040 2LBDSQLC\*MB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10		0		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	99	97
1	115	113	112	110	113	111	110	108	107	106	105	104	103	102	100	100	99	97	97	96	95
2	112	109	106	104	110	107	104	102	104	102	100	101	99	98	98	97	96	95	95	93	92
3	109	105	101	99	107	103	100	98	101	98	96	99	97	95	96	95	93	92	92	91	90
4	106	101	97	95	104	100	97	94	98	95	93	96	94	92	95	93	91	90	89	88	86
5	103	98	94	91	102	97	94	91	95	92	90	94	91	89	93	90	89	88	87	86	84
6	101	95	91	89	99	94	91	88	93	90	88	92	89	87	91	88	87	86	85	84	82
7	98	92	89	86	97	92	88	86	91	88	85	90	87	85	89	86	85	84	83	82	80
8	96	90	86	84	95	90	86	84	89	86	83	88	85	83	87	85	83	82	81	80	79
9	94	88	84	82	93	88	84	82	87	84	82	86	83	81	85	83	81	80	79	79	79
10	92	86	82	80	91	86	82	80	85	82	80	84	82	80	84	81	79	79	79	79	79

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	3913666
5°	3613589
10°	2445948
15°	832136
20°	305650
25°	162023
30°	83281
35°	38869
40°	12742
45°	6409
50°	3013
55°	1148
60°	1317
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P223187

CATALOG NUMBER: LD2B20D010 EU2B20NFL258040 2LBDSQLC\*MB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	790.5	46.4
10°-20°	664.7	39.0
20°-30°	182.4	10.7
30°-40°	53.2	3.1
40°-50°	9.8	0.6
50°-60°	2.2	0.1
60°-70°	0.2	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1637.6	96.2
0°-40°	1690.8	99.3
0°-60°	1702.9	100.0
0°-90°	1703.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1703.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	10104	
5°	9294	791
15°	2075	665
25°	379	182
35°	82	53
45°	12	10
55°	2	2
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P223187

CATALOG NUMBER: LD2B20D010 EU2B20NFL258040 2LBDSQLC\*MB

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	10103.8
1°	10045.1
2°	9941.1
3°	9791.8
4°	9587.2
5°	9293.6
6°	8892.7
7°	8391.1
8°	7778.8
9°	7055.8
10°	6218.7
11°	5301.0
12°	4346.5
13°	3435.6
14°	2658.9
15°	2075.1
17.5°	1170.9
20°	741.5
22.5°	528.4
25°	379.1
27.5°	268.4
30°	186.2
32.5°	130.8
35°	82.2
37.5°	33.6
40°	25.2
42.5°	18.5
45°	11.7
47.5°	6.7
50°	5.0
52.5°	3.4
55°	1.7
57.5°	1.7
60°	1.7
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P223187

CATALOG NUMBER: LD2B20D010 EU2B20NFL258040 2LBDSQLC\*MB

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)