

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P264668

Luminaire Tested: **LD2B15D010 EU2B1510SP158030 2LBDL*MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P264668
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1711-432-2)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B15D010 EU2B1510SP158030 2LBDL*MW
Description: 1500 Lumen, 2inch Portfolio LED Downlight
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1297.0 lumens
Efficiency: N/A
Efficacy: 90.7 lumens/watt
Spacing Criteria (0/90/45): 0.31 / 0.31 / 0.32
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P264668

CATALOG NUMBER: LD2B15D010 EU2B1510SP158030 2LBDL*MW

Luminous Intensity Polar Plot





TEST NUMBER: P264668

CATALOG NUMBER: LD2B15D010 EU2B1510SP158030 2LBDL*MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									20
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			100									
1	115	113	111	110	113	111	110	108	107	106	105	104	103	102	100	99	99	97																			97									
2	112	108	106	103	110	107	104	102	104	102	100	101	99	98	98	97	96	94																			94									
3	109	104	101	98	107	103	100	97	100	98	96	98	96	94	96	94	93	92																			92									
4	105	100	97	94	104	99	96	93	97	95	92	96	93	91	94	92	90	89																			89									
5	103	97	93	91	101	96	93	90	95	92	89	93	91	89	92	90	88	87																			87									
6	100	94	90	88	99	94	90	87	92	89	87	91	88	86	90	88	86	85																			85									
7	98	92	88	85	97	91	88	85	90	87	85	89	86	84	88	86	84	83																			83									
8	95	89	86	83	94	89	85	83	88	85	82	87	84	82	86	84	82	81																			81									
9	93	87	83	81	92	87	83	81	86	83	81	85	82	80	85	82	80	79																			79									
10	91	85	82	79	91	85	81	79	84	81	79	84	81	79	83	80	78	78																			78									

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	4578693
5°	3726580
10°	2013008
15°	802617
20°	321840
25°	154110
30°	79927
35°	42220
40°	23443
45°	14513
50°	9978
55°	6709
60°	5131
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P264668

CATALOG NUMBER: LD2B15D010 EU2B1510SP158030 2LBDL*MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	605.1	46.7
10°-20°	477.4	36.8
20°-30°	140.8	10.9
30°-40°	46.9	3.6
40°-50°	17.6	1.4
50°-60°	7.8	0.6
60°-70°	1.3	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1223.4	94.3
0°-40°	1270.3	97.9
0°-60°	1295.8	99.9
0°-90°	1297.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1297.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	9281	
5°	7525	605
15°	1571	477
25°	283	141
35°	70	47
45°	21	18
55°	8	8
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P264668

CATALOG NUMBER: LD2B15D010 EU2B1510SP158030 2LBDL*MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	9280.6
2.5°	8906.5
5°	7524.7
7.5°	5797.4
10°	4018.2
12.5°	2571.4
15°	1571.4
17.5°	958.4
20°	613.0
22.5°	410.4
25°	283.1
27.5°	200.0
30°	140.3
32.5°	98.7
35°	70.1
37.5°	49.4
40°	36.4
42.5°	28.6
45°	20.8
47.5°	18.2
50°	13.0
52.5°	10.4
55°	7.8
57.5°	7.8
60°	5.2
62.5°	2.6
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)