

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P265102

Luminaire Tested: **LD2B20D010 EU2B2010SP159040 2LBLC\*MB**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P265102  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1711-432-2)  
Test Lab: INNOVATION CENTER(G3)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD2B20D010 EU2B2010SP159040 2LBLC\*MB  
Description: 2000 Lumen, 2inch Portfolio LED Downlight  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1334.0 lumens  
Efficiency: N/A  
Efficacy: 63.8 lumens/watt  
Spacing Criteria (0/90/45): 0.31 / 0.31 / 0.32  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 20.9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P265102

CATALOG NUMBER: LD2B20D010 EU2B2010SP159040 2LBLC\*MB

### Luminous Intensity Polar Plot





TEST NUMBER: P265102

CATALOG NUMBER: LD2B20D010 EU2B2010SP159040 2LBLC\*MB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	115	113	111	110	113	111	110	108	107	106	105	104	103	102	100	99	99	97	97	97	97
2	112	108	106	103	110	107	104	102	104	102	100	101	99	98	98	97	96	94	94	94	94
3	109	104	101	98	107	103	100	97	100	98	96	98	96	94	96	94	93	92	92	92	92
4	105	100	97	94	104	99	96	93	97	95	92	96	93	91	94	92	90	89	89	89	89
5	103	97	93	91	101	96	93	90	95	92	89	93	91	89	92	90	88	87	87	87	87
6	100	94	90	88	99	94	90	87	92	89	87	91	88	86	90	88	86	85	85	85	85
7	98	92	88	85	97	91	88	85	90	87	85	89	86	84	88	86	84	83	83	83	83
8	95	89	86	83	94	89	85	83	88	85	82	87	84	82	86	84	82	81	81	81	81
9	93	87	83	81	92	87	83	81	86	83	81	85	82	80	85	82	80	79	79	79	79
10	91	85	82	79	91	85	81	79	84	81	79	84	81	79	83	80	78	78	78	78	78

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	4709286
5°	3832910
10°	2070420
15°	825551
20°	331028
25°	158519
30°	82206
35°	43425
40°	24087
45°	14931
50°	10285
55°	6881
60°	5230
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P265102

CATALOG NUMBER: LD2B20D010 EU2B2010SP159040 2LBLC\*MB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	622.4	46.7
10°-20°	491.1	36.8
20°-30°	144.9	10.9
30°-40°	48.2	3.6
40°-50°	18.1	1.4
50°-60°	8.0	0.6
60°-70°	1.3	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1258.3	94.3
0°-40°	1306.6	97.9
0°-60°	1332.7	99.9
0°-90°	1334.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1334.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	9545	
5°	7739	622
15°	1616	491
25°	291	145
35°	72	48
45°	21	18
55°	8	8
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P265102

CATALOG NUMBER: LD2B20D010 EU2B2010SP159040 2LBLC\*MB

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	9545.3
2.5°	9160.6
5°	7739.4
7.5°	5962.8
10°	4132.8
12.5°	2644.8
15°	1616.3
17.5°	985.8
20°	630.5
22.5°	422.1
25°	291.2
27.5°	205.7
30°	144.3
32.5°	101.5
35°	72.1
37.5°	50.8
40°	37.4
42.5°	29.4
45°	21.4
47.5°	18.7
50°	13.4
52.5°	10.7
55°	8.0
57.5°	8.0
60°	5.3
62.5°	2.7
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)