

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P264990

Luminaire Tested: **LD2B15D010 EU2B1510SP159030 2LBSQLC*MMS**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P264990
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1711-432-2)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B15D010 EU2B1510SP159030 2LBSQLC*MMS
Description: 1500 Lumen, 2inch Portfolio LED Downlight
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 941.0 lumens
Efficiency: N/A
Efficacy: 65.8 lumens/watt
Spacing Criteria (0/90/45): 0.31 / 0.31 / 0.32
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P264990

CATALOG NUMBER: LD2B15D010 EU2B1510SP159030 2LBSQLC*MMS

Luminous Intensity Polar Plot





TEST NUMBER: P264990

CATALOG NUMBER: LD2B15D010 EU2B1510SP159030 2LBSQLC*MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						100													
1	115	113	111	110	113	111	110	108	107	106	105	104	103	102	100	99	99	97						97													
2	112	108	106	103	110	107	104	102	104	102	100	101	99	98	98	97	96	94						94													
3	109	104	101	98	107	103	100	97	100	98	96	98	96	94	96	94	93	92						92													
4	105	100	97	94	104	99	96	93	97	95	92	96	93	91	94	92	90	89						89													
5	103	97	93	91	101	96	93	90	95	92	89	93	91	89	92	90	88	87						87													
6	100	94	90	88	99	94	90	87	92	89	87	91	88	86	90	88	86	85						85													
7	98	92	88	85	97	91	88	85	90	87	85	89	86	84	88	86	84	83						83													
8	95	89	86	83	94	89	85	83	88	85	82	87	84	82	86	84	82	81						81													
9	93	87	83	81	92	87	83	81	86	83	81	85	82	80	85	82	80	79						79													
10	91	85	82	79	91	85	81	79	84	81	79	84	81	79	83	80	78	78						78													

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	3321904
5°	2703698
10°	1460486
15°	582324
20°	233478
25°	111812
30°	57994
35°	30656
40°	17003
45°	10536
50°	7215
55°	4903
60°	3750
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P264990

CATALOG NUMBER: LD2B15D010 EU2B1510SP159030 2LBSQLC*MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	439.0	46.7
10°-20°	346.4	36.8
20°-30°	102.2	10.9
30°-40°	34.0	3.6
40°-50°	12.8	1.4
50°-60°	5.7	0.6
60°-70°	0.9	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	887.6	94.3
0°-40°	921.6	97.9
0°-60°	940.1	99.9
0°-90°	941.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	941.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6733	
5°	5459	439
15°	1140	346
25°	205	102
35°	51	34
45°	15	13
55°	6	6
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P264990

CATALOG NUMBER: LD2B15D010 EU2B1510SP159030 2LBSQLC*MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	6733.2
2.5°	6461.9
5°	5459.3
7.5°	4206.2
10°	2915.3
12.5°	1865.6
15°	1140.1
17.5°	695.4
20°	444.7
22.5°	297.7
25°	205.4
27.5°	145.1
30°	101.8
32.5°	71.6
35°	50.9
37.5°	35.8
40°	26.4
42.5°	20.7
45°	15.1
47.5°	13.2
50°	9.4
52.5°	7.5
55°	5.7
57.5°	5.7
60°	3.8
62.5°	1.9
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)