

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P#

Luminaire Tested: **LD2B15D010 EU2B15FL409730 2LBD*LI**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P#
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29152)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B15D010 EU2B15FL409730 2LBD*LI
Description: 1500 Lumen, 2inch Portfolio LED Downlight
FLOOD OPTIC
SPUN ROUND TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1025.4 lumens
Efficiency: N/A
Efficacy: 71.7 lumens/watt
Spacing Criteria (0/90/45): 0.59 / 0.59 / 0.58
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P#

CATALOG NUMBER: LD2B15D010 EU2B15FL409730 2LBD*LI

Luminous Intensity Polar Plot





TEST NUMBER: P#

CATALOG NUMBER: LD2B15D010 EU2B15FL409730 2LBD*LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20																	
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR																																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																											
1	114	112	110	108	112	110	108	106	106	105	103	102	101	100	99	98	97	96																											
2	110	106	103	100	108	104	101	99	101	99	97	98	96	95	96	94	93	91																											
3	106	101	96	93	104	99	95	92	97	94	91	94	92	90	92	90	88	87																											
4	102	96	91	88	100	95	90	87	93	89	86	91	88	85	89	86	84	83																											
5	98	91	86	83	97	90	86	83	89	85	82	87	84	81	86	83	81	79																											
6	94	87	82	79	93	86	82	79	85	81	78	84	80	78	83	79	77	76																											
7	91	83	79	75	90	83	78	75	82	78	75	81	77	74	80	76	74	73																											
8	88	80	75	72	87	80	75	72	79	74	71	78	74	71	77	73	71	70																											
9	85	77	72	69	84	76	72	69	76	71	69	75	71	68	74	71	68	67																											
10	82	74	69	66	81	74	69	66	73	69	66	72	68	66	72	68	66	65																											

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	983626
5°	945235
10°	822828
15°	642538
20°	427292
25°	244680
30°	121657
35°	55892
40°	22400
45°	10244
50°	4761
55°	2634
60°	1549
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P#

CATALOG NUMBER: LD2B15D010 EU2B15FL409730 2LBD*LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	221.3	21.6
10°-20°	434.5	42.4
20°-30°	268.9	26.2
30°-40°	80.5	7.8
40°-50°	16.1	1.6
50°-60°	3.9	0.4
60°-70°	0.2	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	924.6	90.2
0°-40°	1005.1	98.0
0°-60°	1025.1	100.0
0°-90°	1025.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1025.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2539	
5°	2431	221
15°	1602	434
25°	572	269
35°	118	80
45°	19	16
55°	4	4
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P#

CATALOG NUMBER: LD2B15D010 EU2B15FL409730 2LBD*LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	2539.4
1°	2525.6
2°	2512.8
3°	2487.2
4°	2463.5
5°	2431.0
6°	2386.7
7°	2330.5
8°	2258.6
9°	2176.8
10°	2092.0
11°	2004.3
12°	1910.7
13°	1813.1
14°	1708.7
15°	1602.3
17.5°	1321.4
20°	1036.6
22.5°	784.4
25°	572.5
27.5°	402.0
30°	272.0
32.5°	179.3
35°	118.2
37.5°	73.9
40°	44.3
42.5°	28.6
45°	18.7
47.5°	11.8
50°	7.9
52.5°	5.9
55°	3.9
57.5°	3.0
60°	2.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P#

CATALOG NUMBER: LD2B15D010 EU2B15FL409730 2LBD*LI

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)