

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P264845

Luminaire Tested: **LD2B20D010 EU2B2010SP158050 2LBSQLC\*MB**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P264845  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1711-432-2)  
Test Lab: INNOVATION CENTER(G3)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD2B20D010 EU2B2010SP158050 2LBSQLC\*MB  
Description: 2000 Lumen, 2inch Portfolio LED Downlight  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1748.0 lumens  
Efficiency: N/A  
Efficacy: 83.6 lumens/watt  
Spacing Criteria (0/90/45): 0.31 / 0.31 / 0.32  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 20.9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P264845

CATALOG NUMBER: LD2B20D010 EU2B2010SP158050 2LBSQLC\*MB

### Luminous Intensity Polar Plot





TEST NUMBER: P264845

CATALOG NUMBER: LD2B20D010 EU2B2010SP158050 2LBSQLC\*MB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	115	113	111	110	113	111	110	108	107	106	105	104	103	102	100	99	99	97	97	97	97
2	112	108	106	103	110	107	104	102	104	102	100	101	99	98	98	97	96	94	94	94	94
3	109	104	101	98	107	103	100	97	100	98	96	98	96	94	96	94	93	92	92	92	92
4	105	100	97	94	104	99	96	93	97	95	92	96	93	91	94	92	90	89	89	89	89
5	103	97	93	91	101	96	93	90	95	92	89	93	91	89	92	90	88	87	87	87	87
6	100	94	90	88	99	94	90	87	92	89	87	91	88	86	90	88	86	85	85	85	85
7	98	92	88	85	97	91	88	85	90	87	85	89	86	84	88	86	84	83	83	83	83
8	95	89	86	83	94	89	85	83	88	85	82	87	84	82	86	84	82	81	81	81	81
9	93	87	83	81	92	87	83	81	86	83	81	85	82	80	85	82	80	79	79	79	79
10	91	85	82	79	91	85	81	79	84	81	79	84	81	79	83	80	78	78	78	78	78

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	6170821
5°	5022392
10°	2712967
15°	1081751
20°	433723
25°	207729
30°	107670
35°	56916
40°	31558
45°	19536
50°	13432
55°	9032
60°	6907
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P264845

CATALOG NUMBER: LD2B20D010 EU2B2010SP158050 2LBSQLC\*MB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	815.6	46.7
10°-20°	643.5	36.8
20°-30°	189.8	10.9
30°-40°	63.2	3.6
40°-50°	23.7	1.4
50°-60°	10.5	0.6
60°-70°	1.7	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1648.8	94.3
0°-40°	1712.0	97.9
0°-60°	1746.3	99.9
0°-90°	1748.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1748.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	12508	
5°	10141	816
15°	2118	643
25°	382	190
35°	94	63
45°	28	24
55°	10	11
65°	0	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P264845

CATALOG NUMBER: LD2B20D010 EU2B2010SP158050 2LBSQLC\*MB

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	12507.7
2.5°	12003.6
5°	10141.2
7.5°	7813.3
10°	5415.4
12.5°	3465.6
15°	2117.9
17.5°	1291.7
20°	826.1
22.5°	553.1
25°	381.6
27.5°	269.5
30°	189.0
32.5°	133.0
35°	94.5
37.5°	66.5
40°	49.0
42.5°	38.5
45°	28.0
47.5°	24.5
50°	17.5
52.5°	14.0
55°	10.5
57.5°	10.5
60°	7.0
62.5°	3.5
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)