

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P225493

Luminaire Tested: **LD2B15D010 EU2B15FL409730 2LBDL*H**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P225493
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14832)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B15D010 EU2B15FL409730 2LBDL*H
Description: 1500 Lumen, 2inch Portfolio LED Downlight
FLOOD OPTIC
LENSED SPUN ROUND TRIM WITH HAZE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 955.4 lumens
Efficiency: N/A
Efficacy: 66.8 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.6
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P225493

CATALOG NUMBER: LD2B15D010 EU2B15FL409730 2LBDL*H

Luminous Intensity Polar Plot





TEST NUMBER: P225493

CATALOG NUMBER: LD2B15D010 EU2B15FL409730 2LBDL*H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95			95
2	110	105	102	99	108	104	101	98	101	98	96	98	96	94	95	93	92	90			90
3	105	100	96	92	103	98	95	91	96	93	90	94	91	89	91	89	87	86			86
4	101	95	90	86	99	94	89	86	91	88	85	90	86	84	88	85	83	82			82
5	97	90	85	81	96	89	84	81	87	83	80	86	82	80	84	81	79	78			78
6	93	86	81	77	92	85	80	77	84	79	76	82	79	76	81	78	75	74			74
7	90	82	77	73	88	81	76	73	80	76	73	79	75	72	78	75	72	71			71
8	86	78	73	70	85	78	73	70	77	72	69	76	72	69	75	71	69	68			68
9	83	75	70	67	82	75	70	67	74	69	66	73	69	66	72	69	66	65			65
10	80	72	67	64	79	72	67	64	71	67	64	70	66	64	70	66	63	62			62

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	839844
5°	811868
10°	716356
15°	564341
20°	387844
25°	234209
30°	126935
35°	65255
40°	31906
45°	15119
50°	7894
55°	5335
60°	3021
65°	1192
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P225493

CATALOG NUMBER: LD2B15D010 EU2B15FL409730 2LBDL*H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	190.8	20.0
10°-20°	383.1	40.1
20°-30°	256.0	26.8
30°-40°	92.7	9.7
40°-50°	23.9	2.5
50°-60°	7.1	0.7
60°-70°	1.8	0.2
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	829.9	86.9
0°-40°	922.6	96.6
0°-60°	953.6	99.8
0°-90°	955.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	955.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2168	
5°	2088	191
15°	1407	383
25°	548	256
35°	138	93
45°	28	24
55°	8	7
65°	1	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P225493

CATALOG NUMBER: LD2B15D010 EU2B15FL409730 2LBDL*H

CANDELA DISTRIBUTION (FULL):

	0°
0°	2168.2
2.5°	2148.5
5°	2088.0
7.5°	1977.6
10°	1821.3
12.5°	1629.4
15°	1407.3
17.5°	1170.8
20°	940.9
22.5°	729.3
25°	548.0
27.5°	399.5
30°	283.8
32.5°	199.7
35°	138.0
37.5°	95.9
40°	63.1
42.5°	40.7
45°	27.6
47.5°	19.7
50°	13.1
52.5°	10.5
55°	7.9
57.5°	5.3
60°	3.9
62.5°	2.6
65°	1.3
67.5°	1.3
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)