

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224984

Luminaire Tested: **LD2B15D010 EU2B15FL409730 2LBDL*LI**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P224984
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (152)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B15D010 EU2B15FL409730 2LBDL*LI
Description: 1500 Lumen, 2inch Portfolio LED Downlight
FLOOD OPTIC
LENSED SPUN ROUND TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 962.6 lumens
Efficiency: N/A
Efficacy: 67.3 lumens/watt
Spacing Criteria (0/90/45): 0.59 / 0.59 / 0.58
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P224984

CATALOG NUMBER: LD2B15D010 EU2B15FL409730 2LBDL*LI

Luminous Intensity Polar Plot





TEST NUMBER: P224984

CATALOG NUMBER: LD2B15D010 EU2B15FL409730 2LBDL*LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	114	112	110	108	112	110	108	106	106	105	103	102	101	100	99	98	97	96			96
2	110	106	103	100	108	104	101	99	101	99	97	98	96	95	96	94	93	91			91
3	106	101	96	93	104	99	95	92	97	94	91	94	92	90	92	90	88	87			87
4	102	96	91	88	100	95	90	87	93	89	86	91	88	85	89	86	84	83			83
5	98	91	86	83	97	90	86	83	89	85	82	87	84	81	86	83	81	79			79
6	94	87	82	79	93	86	82	79	85	81	78	84	80	78	83	79	77	76			76
7	91	83	79	75	90	83	78	75	82	78	75	81	77	74	80	76	74	73			73
8	88	80	75	72	87	80	75	72	79	74	71	78	74	71	77	73	71	70			70
9	85	77	72	69	84	76	72	69	76	71	69	75	71	68	74	71	68	67			67
10	82	74	69	66	81	74	69	66	73	69	66	72	68	66	72	68	66	65			65

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	923394
5°	887339
10°	772444
15°	603159
20°	401158
25°	229722
30°	114188
35°	52488
40°	21035
45°	9641
50°	4459
55°	2499
60°	1472
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P224984

CATALOG NUMBER: LD2B15D010 EU2B15FL409730 2LBDL*LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	207.7	21.6
10°-20°	407.9	42.4
20°-30°	252.4	26.2
30°-40°	75.5	7.8
40°-50°	15.1	1.6
50°-60°	3.7	0.4
60°-70°	0.2	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	868.0	90.2
0°-40°	943.6	98.0
0°-60°	962.4	100.0
0°-90°	962.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	962.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2384	
5°	2282	208
15°	1504	408
25°	538	252
35°	111	76
45°	18	15
55°	4	4
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P224984

CATALOG NUMBER: LD2B15D010 EU2B15FL409730 2LBDL*LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	2383.9
1°	2370.9
2°	2358.9
3°	2334.8
4°	2312.6
5°	2282.1
6°	2240.5
7°	2187.8
8°	2120.2
9°	2043.4
10°	1963.9
11°	1881.6
12°	1793.7
13°	1702.1
14°	1604.0
15°	1504.1
17.5°	1240.5
20°	973.2
22.5°	736.3
25°	537.5
27.5°	377.4
30°	255.3
32.5°	168.4
35°	111.0
37.5°	69.4
40°	41.6
42.5°	26.8
45°	17.6
47.5°	11.1
50°	7.4
52.5°	5.6
55°	3.7
57.5°	2.8
60°	1.9
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P224984

CATALOG NUMBER: LD2B15D010 EU2B15FL409730 2LBDL*LI

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)