

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P223070

Luminaire Tested: **LD2B20D010 EU2B20NFL258050 2LBDL*WMH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P223070
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (155)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B20D010 EU2B20NFL258050 2LBDL*WMH
Description: 2000 Lumen, 2inch Portfolio LED Downlight
NARROW FLOOD OPTIC
LENSED SPUN ROUND TRIM WITH WHEAT METALLIC HAZE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1817.0 lumens
Efficiency: N/A
Efficacy: 86.9 lumens/watt
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.35
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P223070

CATALOG NUMBER: LD2B20D010 EU2B20NFL258050 2LBDL*WMH

Luminous Intensity Polar Plot





TEST NUMBER: P223070

CATALOG NUMBER: LD2B20D010 EU2B20NFL258050 2LBDL*WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100															
1	115	113	112	110	113	111	110	108	107	106	105	104	103	102	100	100	99	97				97															
2	112	109	106	104	110	107	104	102	104	102	100	101	99	98	98	97	96	95				95															
3	109	105	101	99	107	103	100	98	101	98	96	99	97	95	96	95	93	92				92															
4	106	101	97	95	104	100	97	94	98	95	93	96	94	92	95	93	91	90				90															
5	103	98	94	91	102	97	94	91	95	92	90	94	91	89	93	90	89	88				88															
6	101	95	91	89	99	94	91	88	93	90	88	92	89	87	91	88	87	86				86															
7	98	92	89	86	97	92	88	86	91	88	85	90	87	85	89	86	85	84				84															
8	96	90	86	84	95	90	86	84	89	86	83	88	85	83	87	85	83	82				82															
9	94	88	84	82	93	88	84	82	87	84	82	86	83	81	85	83	81	80				80															
10	92	86	82	80	91	86	82	80	85	82	80	84	82	80	84	81	79	79				79															

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	4175435
5°	3855245
10°	2609491
15°	887796
20°	326095
25°	172879
30°	88872
35°	41470
40°	13551
45°	6847
50°	3254
55°	1216
60°	1394
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P223070

CATALOG NUMBER: LD2B20D010 EU2B20NFL258050 2LBDL*WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	843.4	46.4
10°-20°	709.1	39.0
20°-30°	194.6	10.7
30°-40°	56.7	3.1
40°-50°	10.5	0.6
50°-60°	2.4	0.1
60°-70°	0.2	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1747.2	96.2
0°-40°	1803.9	99.3
0°-60°	1816.8	100.0
0°-90°	1817.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1817.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	10780	
5°	9915	843
15°	2214	709
25°	404	195
35°	88	57
45°	12	11
55°	2	2
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P223070

CATALOG NUMBER: LD2B20D010 EU2B20NFL258050 2LBDL*WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	10779.6
1°	10716.9
2°	10606.0
3°	10446.7
4°	10228.3
5°	9915.1
6°	9487.4
7°	8952.3
8°	8299.0
9°	7527.6
10°	6634.5
11°	5655.6
12°	4637.2
13°	3665.4
14°	2836.7
15°	2213.9
17.5°	1249.2
20°	791.1
22.5°	563.8
25°	404.5
27.5°	286.4
30°	198.7
32.5°	139.6
35°	87.7
37.5°	35.8
40°	26.8
42.5°	19.7
45°	12.5
47.5°	7.2
50°	5.4
52.5°	3.6
55°	1.8
57.5°	1.8
60°	1.8
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P223070

CATALOG NUMBER: LD2B20D010 EU2B20NFL258050 2LBDL*WMH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)