

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P#

Luminaire Tested: **LD2B15D010 EU2B15WFL559730 2LBDL*H**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P#
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14807)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B15D010 EU2B15WFL559730 2LBDL*H
Description: 1500 Lumen, 2inch Portfolio LED Downlight
WIDE FLOOD OPTIC
LENSED SPUN ROUND TRIM WITH HAZE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 890.7 lumens
Efficiency: N/A
Efficacy: 62.3 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P#

CATALOG NUMBER: LD2B15D010 EU2B15WFL559730 2LBDL*H

Luminous Intensity Polar Plot





TEST NUMBER: P#

CATALOG NUMBER: LD2B15D010 EU2B15WFL559730 2LBDL*H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|---|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | | | 0 | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | | |
| 1 | 113 | 111 | 108 | 106 | 111 | 108 | 106 | 104 | 104 | 102 | 101 | 101 | 99 | 98 | 97 | 96 | 95 | 93 | | | |
| 2 | 108 | 102 | 98 | 95 | 105 | 101 | 97 | 94 | 98 | 94 | 92 | 95 | 92 | 90 | 92 | 90 | 88 | 86 | | | |
| 3 | 102 | 95 | 90 | 86 | 100 | 94 | 89 | 85 | 91 | 87 | 84 | 89 | 85 | 83 | 86 | 84 | 81 | 80 | | | |
| 4 | 96 | 89 | 83 | 79 | 95 | 87 | 82 | 78 | 85 | 81 | 77 | 83 | 79 | 76 | 81 | 78 | 75 | 74 | | | |
| 5 | 91 | 83 | 77 | 72 | 90 | 82 | 76 | 72 | 80 | 75 | 71 | 78 | 74 | 71 | 77 | 73 | 70 | 68 | | | |
| 6 | 87 | 77 | 71 | 67 | 85 | 77 | 71 | 67 | 75 | 70 | 66 | 74 | 69 | 66 | 72 | 68 | 65 | 64 | | | |
| 7 | 82 | 73 | 66 | 62 | 81 | 72 | 66 | 62 | 71 | 65 | 62 | 69 | 65 | 61 | 68 | 64 | 61 | 59 | | | |
| 8 | 78 | 68 | 62 | 58 | 77 | 68 | 62 | 58 | 67 | 61 | 57 | 66 | 61 | 57 | 65 | 60 | 57 | 56 | | | |
| 9 | 74 | 64 | 58 | 54 | 73 | 64 | 58 | 54 | 63 | 58 | 54 | 62 | 57 | 54 | 61 | 57 | 54 | 52 | | | |
| 10 | 71 | 61 | 55 | 51 | 70 | 60 | 55 | 51 | 60 | 54 | 51 | 59 | 54 | 51 | 58 | 54 | 50 | 49 | | | |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|--------|
| | 0° |
| 0° | 417830 |
| 5° | 409744 |
| 10° | 380892 |
| 15° | 337209 |
| 20° | 291924 |
| 25° | 245407 |
| 30° | 192191 |
| 35° | 137319 |
| 40° | 91673 |
| 45° | 56861 |
| 50° | 34047 |
| 55° | 20395 |
| 60° | 9141 |
| 65° | 1192 |
| 70° | 0 |
| 75° | 0 |
| 80° | 0 |
| 85° | 0 |



TEST NUMBER: P#

CATALOG NUMBER: LD2B15D010 EU2B15WFL559730 2LBDL*H

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 97.8 | 11.0 |
| 10°-20° | 234.2 | 26.3 |
| 20°-30° | 261.2 | 29.3 |
| 30°-40° | 183.0 | 20.5 |
| 40°-50° | 83.5 | 9.4 |
| 50°-60° | 27.9 | 3.1 |
| 60°-70° | 3.0 | 0.3 |
| 70°-80° | 0.0 | 0.0 |
| 80°-90° | 0.0 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 593.2 | 66.6 |
| 0°-40° | 776.2 | 87.1 |
| 0°-60° | 887.6 | 99.7 |
| 0°-90° | 890.7 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 890.7 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 1079 | |
| 5° | 1054 | 98 |
| 15° | 841 | 234 |
| 25° | 574 | 261 |
| 35° | 290 | 183 |
| 45° | 104 | 84 |
| 55° | 30 | 28 |
| 65° | 1 | 3 |
| 75° | 0 | 0 |
| 85° | 0 | 0 |
| 90° | 0 | |



TEST NUMBER: P#

CATALOG NUMBER: LD2B15D010 EU2B15WFL559730 2LBDL*H

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|--------|
| 0° | 1078.7 |
| 2.5° | 1073.5 |
| 5° | 1053.8 |
| 7.5° | 1017.0 |
| 10° | 968.4 |
| 12.5° | 906.6 |
| 15° | 840.9 |
| 17.5° | 772.6 |
| 20° | 708.2 |
| 22.5° | 643.8 |
| 25° | 574.2 |
| 27.5° | 503.2 |
| 30° | 429.7 |
| 32.5° | 357.4 |
| 35° | 290.4 |
| 37.5° | 231.3 |
| 40° | 181.3 |
| 42.5° | 138.0 |
| 45° | 103.8 |
| 47.5° | 77.5 |
| 50° | 56.5 |
| 52.5° | 40.7 |
| 55° | 30.2 |
| 57.5° | 21.0 |
| 60° | 11.8 |
| 62.5° | 3.9 |
| 65° | 1.3 |
| 67.5° | 1.3 |
| 70° | 0.0 |
| 72.5° | 0.0 |
| 75° | 0.0 |
| 77.5° | 0.0 |
| 80° | 0.0 |
| 82.5° | 0.0 |
| 85° | 0.0 |
| 87.5° | 0.0 |
| 90° | 0.0 |



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)