

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P223079

Luminaire Tested: **LD2B20D010 EU2B20NFL258050 2LBDSQLC*MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P223079
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (155)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B20D010 EU2B20NFL258050 2LBDSQLC*MW
Description: 2000 Lumen, 2inch Portfolio LED Downlight
NARROW FLOOD OPTIC
LENSED SQUARE CAST TRIM WITH MATTE WHITE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1712.8 lumens
Efficiency: N/A
Efficacy: 82.0 lumens/watt
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.35
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P223079

CATALOG NUMBER: LD2B20D010 EU2B20NFL258050 2LBDSQLC*MW

Luminous Intensity Polar Plot





TEST NUMBER: P223079

CATALOG NUMBER: LD2B20D010 EU2B20NFL258050 2LBDSQLC*MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	99	97
1	115	113	112	110	113	111	110	108	107	106	105	104	103	102	100	100	99	97	97	96	95
2	112	109	106	104	110	107	104	102	104	102	100	101	99	98	98	97	96	95	95	93	92
3	109	105	101	99	107	103	100	98	101	98	96	99	97	95	96	95	93	92	92	91	90
4	106	101	97	95	104	100	97	94	98	95	93	96	94	92	95	93	91	90	89	88	88
5	103	98	94	91	102	97	94	91	95	92	90	94	91	89	93	90	89	88	87	86	86
6	101	95	91	89	99	94	91	88	93	90	88	92	89	87	91	88	87	86	85	84	84
7	98	92	89	86	97	92	88	86	91	88	85	90	87	85	89	86	85	84	83	82	82
8	96	90	86	84	95	90	86	84	89	86	83	88	85	83	87	85	83	82	81	80	80
9	94	88	84	82	93	88	84	82	87	84	82	86	83	81	85	83	81	80	79	79	79
10	92	86	82	80	91	86	82	80	85	82	80	84	82	80	84	81	79	79	79	79	79

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	3935978
5°	3634158
10°	2459872
15°	836868
20°	307381
25°	162963
30°	83773
35°	39106
40°	12793
45°	6464
50°	3073
55°	1148
60°	1317
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P223079

CATALOG NUMBER: LD2B20D010 EU2B20NFL258050 2LBDSQLC*MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	795.0	46.4
10°-20°	668.5	39.0
20°-30°	183.4	10.7
30°-40°	53.5	3.1
40°-50°	9.9	0.6
50°-60°	2.3	0.1
60°-70°	0.2	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1647.0	96.2
0°-40°	1700.5	99.3
0°-60°	1712.6	100.0
0°-90°	1712.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1712.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	10161	
5°	9346	795
15°	2087	668
25°	381	183
35°	83	53
45°	12	10
55°	2	2
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P223079

CATALOG NUMBER: LD2B20D010 EU2B20NFL258050 2LBDSQLC*MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	10161.4
1°	10102.3
2°	9997.7
3°	9847.6
4°	9641.8
5°	9346.5
6°	8943.3
7°	8438.9
8°	7823.1
9°	7095.9
10°	6254.1
11°	5331.2
12°	4371.3
13°	3455.2
14°	2674.1
15°	2086.9
17.5°	1177.6
20°	745.7
22.5°	531.4
25°	381.3
27.5°	269.9
30°	187.3
32.5°	131.6
35°	82.7
37.5°	33.7
40°	25.3
42.5°	18.6
45°	11.8
47.5°	6.7
50°	5.1
52.5°	3.4
55°	1.7
57.5°	1.7
60°	1.7
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P223079

CATALOG NUMBER: LD2B20D010 EU2B20NFL258050 2LBDSQLC*MW

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)