

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P264046

Luminaire Tested: **LD2B15D010 EU2B1510SP158035 2LBD\*WH**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P264046  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1805-787-1)  
Test Lab: INNOVATION CENTER(G2)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD2B15D010 EU2B1510SP158035 2LBD\*WH  
Description: 1500 Lumen, 2inch Portfolio LED Downlight  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1310.9 lumens  
Efficiency: N/A  
Efficacy: 91.7 lumens/watt  
Spacing Criteria (0/90/45): 0.28 / 0.28 / 0.28  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 14.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P264046

CATALOG NUMBER: LD2B15D010 EU2B1510SP158035 2LBD\*WH

### Luminous Intensity Polar Plot





TEST NUMBER: P264046

CATALOG NUMBER: LD2B15D010 EU2B1510SP158035 2LBD\*WH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	116	114	112	111	113	112	110	109	108	107	106	104	103	102	101	100	100	98	98	98	98
2	113	109	107	105	111	108	106	104	105	103	101	102	101	99	99	98	97	96	96	96	96
3	110	106	103	100	108	105	102	100	102	100	98	100	98	97	98	96	95	94	94	94	94
4	107	103	99	97	106	102	99	96	100	97	95	98	96	94	96	95	93	92	92	92	92
5	105	100	97	94	104	99	96	94	98	95	93	96	94	92	95	93	91	90	90	90	90
6	103	98	94	92	102	97	94	91	96	93	91	95	92	90	93	91	90	89	89	89	89
7	101	95	92	90	100	95	92	89	94	91	89	93	90	89	92	90	88	87	87	87	87
8	99	93	90	88	98	93	90	88	92	89	87	91	89	87	91	88	87	86	86	86	86
9	97	92	88	86	96	91	88	86	91	88	86	90	87	86	89	87	85	85	85	85	85
10	95	90	87	85	95	90	87	85	89	86	85	89	86	84	88	86	84	83	83	83	83

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	6186115
5°	4958456
10°	2164152
15°	670686
20°	233793
25°	103266
30°	46771
35°	24332
40°	13847
45°	6559
50°	4145
55°	2322
60°	1283
65°	1518
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P264046

CATALOG NUMBER: LD2B15D010 EU2B1510SP158035 2LBD\*WH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	760.3	58.0
10°-20°	416.4	31.8
20°-30°	94.9	7.2
30°-40°	27.3	2.1
40°-50°	8.4	0.6
50°-60°	2.5	0.2
60°-70°	1.1	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1271.6	97.0
0°-40°	1298.9	99.1
0°-60°	1309.8	99.9
0°-90°	1310.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1310.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	12539	
5°	10012	760
15°	1313	416
25°	190	95
35°	40	27
45°	9	8
55°	3	3
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P264046

CATALOG NUMBER: LD2B15D010 EU2B1510SP158035 2LBD\*WH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	12538.7
1°	12382.6
2°	12058.4
3°	11555.2
4°	10863.7
5°	10012.1
6°	8968.1
7°	7801.7
8°	6584.1
9°	5405.6
10°	4319.9
11°	3401.0
12°	2677.2
13°	2106.8
14°	1664.2
15°	1313.1
16°	1035.9
17°	824.7
18°	663.3
19°	539.5
20°	445.3
22.5°	287.9
25°	189.7
26°	160.1
27°	135.9
28°	114.4
29°	95.5
30°	82.1
32.5°	56.5
35°	40.4
37.5°	29.6
40°	21.5
42.5°	14.8
45°	9.4
47.5°	6.7
50°	5.4
52.5°	4.0
55°	2.7
57.5°	1.3
60°	1.3
62.5°	1.3
65°	1.3
67.5°	1.3



TEST NUMBER: P264046

CATALOG NUMBER: LD2B15D010 EU2B1510SP158035 2LBD\*WH

**CANDELA DISTRIBUTION (continued):**

	0°
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







70°		0.0
72.5°		0.0



(END OF REPORT)