

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P264730

Luminaire Tested: **LD2B15D010 EU2B1510SP158035 2LBSQLC*MMS**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P264730
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1711-432-2)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B15D010 EU2B1510SP158035 2LBSQLC*MMS
Description: 1500 Lumen, 2inch Portfolio LED Downlight
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1180.0 lumens
Efficiency: N/A
Efficacy: 82.5 lumens/watt
Spacing Criteria (0/90/45): 0.31 / 0.31 / 0.32
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P264730

CATALOG NUMBER: LD2B15D010 EU2B1510SP158035 2LBSQLC*MMS

Luminous Intensity Polar Plot





TEST NUMBER: P264730

CATALOG NUMBER: LD2B15D010 EU2B1510SP158035 2LBSQLC*MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100											100																	
1	115	113	111	110	113	111	110	108	107	106	105	104	103	102	100	99	99	97											97																	
2	112	108	106	103	110	107	104	102	104	102	100	101	99	98	98	97	96	94											94																	
3	109	104	101	98	107	103	100	97	100	98	96	98	96	94	96	94	93	92											92																	
4	105	100	97	94	104	99	96	93	97	95	92	96	93	91	94	92	90	89											89																	
5	103	97	93	91	101	96	93	90	95	92	89	93	91	89	92	90	88	87											87																	
6	100	94	90	88	99	94	90	87	92	89	87	91	88	86	90	88	86	85											85																	
7	98	92	88	85	97	91	88	85	90	87	85	89	86	84	88	86	84	83											83																	
8	95	89	86	83	94	89	85	83	88	85	82	87	84	82	86	84	82	81											81																	
9	93	87	83	81	92	87	83	81	86	83	81	85	82	80	85	82	80	79											79																	
10	91	85	82	79	91	85	81	79	84	81	79	84	81	79	83	80	78	78											78																	

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	4165651
5°	3390407
10°	1831406
15°	730242
20°	292806
25°	140228
30°	72692
35°	38426
40°	21318
45°	13187
50°	9057
55°	6107
60°	4638
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P264730

CATALOG NUMBER: LD2B15D010 EU2B1510SP158035 2LBSQLC*MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	550.6	46.7
10°-20°	434.4	36.8
20°-30°	128.1	10.9
30°-40°	42.7	3.6
40°-50°	16.0	1.4
50°-60°	7.1	0.6
60°-70°	1.1	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1113.1	94.3
0°-40°	1155.7	97.9
0°-60°	1178.9	99.9
0°-90°	1180.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1180.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8443	
5°	6846	551
15°	1430	434
25°	258	128
35°	64	43
45°	19	16
55°	7	7
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P264730

CATALOG NUMBER: LD2B15D010 EU2B1510SP158035 2LBSQLC*MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	8443.4
2.5°	8103.1
5°	6845.9
7.5°	5274.5
10°	3655.7
12.5°	2339.5
15°	1429.7
17.5°	872.0
20°	557.7
22.5°	373.4
25°	257.6
27.5°	182.0
30°	127.6
32.5°	89.8
35°	63.8
37.5°	44.9
40°	33.1
42.5°	26.0
45°	18.9
47.5°	16.5
50°	11.8
52.5°	9.5
55°	7.1
57.5°	7.1
60°	4.7
62.5°	2.4
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)