

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224948

Luminaire Tested: **LD2B15D010 EU2B15FL408035 2LBD*H**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P224948
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (156)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B15D010 EU2B15FL408035 2LBD*H
Description: 1500 Lumen, 2inch Portfolio LED Downlight
FLOOD OPTIC
SPUN ROUND TRIM WITH HAZE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1390.0 lumens
Efficiency: N/A
Efficacy: 97.2 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P224948

CATALOG NUMBER: LD2B15D010 EU2B15FL408035 2LBD*H

Luminous Intensity Polar Plot





TEST NUMBER: P224948

CATALOG NUMBER: LD2B15D010 EU2B15FL408035 2LBD*H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95				95
2	110	106	103	100	108	104	101	99	101	99	97	98	96	94	96	94	93	91				91
3	106	100	96	93	104	99	95	92	97	94	91	94	92	90	92	90	88	87				87
4	102	96	91	88	100	94	90	87	92	89	86	91	88	85	89	86	84	83				83
5	98	91	86	83	96	90	86	82	89	85	82	87	84	81	86	83	80	79				79
6	94	87	82	79	93	86	82	78	85	81	78	84	80	77	82	79	77	76				76
7	91	83	78	75	90	83	78	75	82	77	74	80	77	74	79	76	74	73				73
8	88	80	75	72	87	79	75	72	78	74	71	77	74	71	77	73	71	70				70
9	85	77	72	69	84	76	72	69	75	71	68	75	71	68	74	70	68	67				67
10	82	74	69	66	81	73	69	66	73	69	66	72	68	66	71	68	65	64				64

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1289281
5°	1262283
10°	1111723
15°	872197
20°	579230
25°	332509
30°	166742
35°	77029
40°	31299
45°	14023
50°	7292
55°	4525
60°	2092
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P224948

CATALOG NUMBER: LD2B15D010 EU2B15FL408035 2LBD*H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	296.5	21.3
10°-20°	588.7	42.4
20°-30°	365.8	26.3
30°-40°	110.3	7.9
40°-50°	22.6	1.6
50°-60°	5.8	0.4
60°-70°	0.3	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1251.0	90.0
0°-40°	1361.3	97.9
0°-60°	1389.7	100.0
0°-90°	1390.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1390.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3328	
5°	3246	297
15°	2175	589
25°	778	366
35°	163	110
45°	26	23
55°	7	6
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P224948

CATALOG NUMBER: LD2B15D010 EU2B15FL408035 2LBD*H

CANDELA DISTRIBUTION (FULL):

	0°
0°	3328.5
1°	3317.7
2°	3302.9
3°	3292.2
4°	3276.0
5°	3246.4
6°	3199.3
7°	3134.7
8°	3041.8
9°	2936.8
10°	2826.5
11°	2709.4
12°	2586.9
13°	2459.0
14°	2319.0
15°	2175.0
17.5°	1788.7
20°	1405.2
22.5°	1066.0
25°	778.0
27.5°	549.1
30°	372.8
32.5°	245.0
35°	162.9
37.5°	100.9
40°	61.9
42.5°	40.4
45°	25.6
47.5°	16.2
50°	12.1
52.5°	8.1
55°	6.7
57.5°	4.0
60°	2.7
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P224948

CATALOG NUMBER: LD2B15D010 EU2B15FL408035 2LBD*H

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)